



SIGN	DATE	DESCRIPTION	APPROVER
1	2010.03.09	Added cULus logo	Jacke
2	2010.03.09	The material is changed from Brass to Copper	Jacke
3	2010.03.09	The design is changed	Jacke
4	2010.03.09	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			









Material

- Item ⓐ Clamp : Brass(CuZn) Ni plated
- Item ⓑ Terminal screw:Steel Zinc plating"-"slot type
- 2 Item ⓒ Female contact : Copper Tin plated
- Item ⓓ Terminal (body):Thermoplastic (UL94V-0)
- Item ⓔ Terminal (cover):Thermoplastic (UL94V-0)
- Item ⓕ With flange screw:Steel Zinc plating M3 "*"slot type

Electrical cULus

- Voltage rating: 300V
- Current rating: 20A
- Wire range:
- Solid wire(AWG):10-30
- Stranded wire(AWG):10-30
- Torque: 4.5(Lb-In)
- Screw:M3
- Wire strip length:7-8mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- 1 Safety Approval: c UL us

VB xx 01 x 2 xxxx G

02	2 CONTACTS	0	Black (RAL9005)	0000: "@" Logo	RoHS
03	3 CONTACTS	2	Red (RAL3001/D)	000A: "ANYTEK" Logo	Pb<40,000ppm
...	...	3	Orange(RAL2011/P)	Any special item by	
16	16 CONTACTS	4	Yellow(RAL1018/A)	customer requst.	
		5	Green(RAL6018/T)	please contact sales	
		6	Blue (RAL5015/A)	department.	
		8	Grey(RAL7035/D)		

N = Number of poles
Dim A=Nx7.62
Dim B=(N-1)x7.62

	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.30	±0.30
13-16p	±0.40	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VB-7.62 SERIES With flange				
PART NO.	VBxx01x2xxxxG			DWG NO.	8VB0002
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacke 2010.03.10	Jacke 2010.03.10	UNIT: mm	
				SCALE: NONE	
				SHEET: 01/01	REV.: C

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°