1326122-1 ✔ ACTIVE


AMP | AMP 0.64 Connector System

TE Internal #: 1326122-1

Shield Assembly, 70° Cable Exit, Black, Nylon GF, 52 Position, AMP 0.64 Connector System

View on TE.com >

Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Shield Assembly**

Cable Exit Angle: **70°**

Strain Relief: **With**

Primary Product Color: **Black**

Primary Product Material: **Nylon GF**

Features

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Serviceable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Configuration Features

Compatible With Connector Code	A-E
Number of Positions	52

Product Type Features

Protection & Strain Relief Accessory Type	Shield Assembly

Body Features

Cable Exit Angle	70°
Primary Product Color	Black
Primary Product Material	Nylon GF

Mechanical Attachment

Strain Relief	With

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1326042-2
LAC CARRIER, 26 POS, 0.64MM, B KEY



TE Part # 1326042-1
LAC CARRIER, 26 POS, 0.64MM, A KEY

TE Part # 1326120-1
52WAY LAC "SINGLE GEAR" LEVER

Also in the Series | AMP 0.64 Connector System




Automotive Connector Caps & Covers (9)



Automotive Headers(5)




Automotive Housings(14)




Automotive Terminals(8)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(5)



Wire-to-Board Headers & Receptacles (5)

Customers Also Bought



TE Part #2-2834074-3
3P PLUG, MINIATURE WATERPROOF CONN,BLACK




TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #2-2834075-3
3P REC, MINIATURE WATERPROOF CONN,BLACK




TE Part #2-1879071-3
THS50 6R8 5%



TE Part #965643-1
ABDECKKAPPE F42P




TE Part #963225-1
DICHTUNG F 42P GEH



TE Part #929975-1
BU-KONTAKT 2,5MMD



TE Part #964286-2
JPT A REC 2.8 Contact SWS Sn



TE Part #963222-1
SEALING F/29P HSG

Documents

Product Drawings

52WAY LAC "SINGLE GEAR" SHIELD

English

CAD Files

Customer View Model

ENG_CVM_CVM_1326122-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1326122-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1326122-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Instruction Sheets

Instruction Sheet (U.S.)

English