



SIGN	DATE	DESCRIPTION	APPROVER
1	01/24'07	The Soldering temperature from 245° to 250°	Aaron
2	01/02'13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	









2 P.C.B. LAYOUT
Top view

2 Material

Item 1	Insulating body	Thermoplastic (UL94V-0)
Item 2	Insulating cover	Thermoplastic (UL94V-0)
Item 3	Insulating lever	Thermoplastic (UL94V-0) Natural color
Item 4	Insulating partition	Thermoplastic (UL94V-0)
Item 5	Contact pin	Brass, Tin plated
Item 6	Spring clamp	Stainless steel

2 Electrica cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire: 2×AWG 18-24
- Stranded wire: 2×AWG 18-24
- Pull force:
- Screw:
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- 1 Safety Approval: c UL us
- Critical dimension: ▽

HB x x 1 2 x 0 xxxx G

- 2 RoHs compliant (lead<4%) In copper Alloy

No. OF POLES
02: 2 POLES
03: 3 POLES
:
:
12: 12 POLES

2 Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by customer request, please contact sales department.

2 N=NUMBER OF POLES

Dim L	(N-1)×10.0+6.0
Dim B	(N-1)×10.0

	Dim L	Dim B
2-4p	±0.25	±0.15
5-8p	±0.35	±0.25
9-12p	±0.45	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HB -10.0mm Series (Double wire)				
PART NO.	HBxx12x0xxxxG			DWG NO.	8HB0202
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.01.02	Da cheng 2013.01.02	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: D	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°