

RECOMMENDED PCB LAYOUT

Specifications

A. Material

Plastic cement: PBT, 94V-0, White

Contact: Copper Alloy, T=0.25mm

Shell: SPCC, T=0.30mm

B. Plating

Contact Area: 1u" Au over 50u' min. Nickel

Solder Tails: 100u" min. Matte Tinover 50u' min. Nickel

Shell: 80u" min. Nickel

C. Electrical

Current Rating: 1.5A/contact terminal

Voltage Rating: 30V

Power Rating: 45W

Contact Resistance: 40mΩ max initial
50mΩ max after test

Dielectric Withstanding Voltage: 100V AC

Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental



Operating Temperature: -25℃ to +85℃

Insertion force: 35.7 N Max


Withdrawal force: 10.2 N Min


Contact retention: 4.5N Min

Durability: 1500 cycles



Pin Numbe	Signal Name
1	VBUS
2	D-
3	D+
4	GND




Part Number			Product Description				 Connecting the Future www.szywf.com.cn www.szywf.cn	
PUBFA-R23F-075			USB 2.0 Receptacle, Type A, Flag Type, 4 Pin, Thru-Hole, With Kinked Shell Stakes					
DWG.No.	P-UBF-273		Tolerances Unspecified			Units: Metric(mm)		
Revision	A0		X.X ±0.35	X° ±5°				
Designed	Lee	11/26/20	X.XX ±0.25	X.X° ±2°				
Approved	Allen	11/26/20	X.XXX ±0.15					
							Sheet No. 1/2	




www.szywf.com.cn
www.szywf.cn

Sheet No. 1/2




② 200pcs/box, four sides and stapled.


③ 15 box/case (3K pcs).



⑥ Paste the product or ROHS label as shown.



⑤ The outer box is sealed with transparent adhesive tape in the shape of "H".



④ 15 boxes per box * 1, if the last box is added with filler in the space.

Part Number			Product Description			
PUBFA-R23F-075			USB 2.0 Receptacle, Type A, Flag Type, 4 Pin, Thru-Hole, With Kinked Shell Stakes			
DWG.No.	P-UBF-273		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X	±0.35		
Designed	Lee	11/26/20	X.XX	±0.25	X°	±5°
Approved	Allen	11/26/20	X.XXX	±0.15	X.X°	±2°

