






SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100m\Omega$.
3. Insulation resistance: $\geq 100M\Omega$ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $250\pm 80gf$
6. Travel: $0.25\pm 0.1mm$.
7. life test: 10,000 cycles.
8. Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
9. Sign"* "is importance dimension.



CIRCUIT DIAGRAM



P . C . B LAYOUT

H=8.0mm

				TOLERANCE UNLESS SPECIFIED							
				<1.5: $\pm 0.1mm$	ANGULAR $\pm 1^{\circ}$	A1	2023.2.17	更新图纸		WM	
				>1.5~5.0: $\pm 0.25mm$		NO	DATE	REVISIONS		BY	APPD
1	TERMINAL	BRASS	1	Ag-PLATED	TITLE: TACT SWITCH		UNIT : MM	ROHS	DWN		
2	CASE	PA9T	1	BLACK	MODEL: TC-00104-080E		SCALE: 1:1	COMPLIANT	CHK'D		
3	CONTACT	SUS301	1	Ag-PLATED	DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOUYA		东莞市弘皓电子有限公司		APPD		
4	COVER	BRASS	1	Sn-PLATED					PRO.AGL:		
5	KNOB	PA9T	1	BLACK							
NO.	PART	NAME	MATERIAL	QTY	FINISHING						