Specifications







Eaton 25ET

Eaton Bussmann series high speed British standard fuse, high speed, 25 A, AC 690 V, DC 500 V, BS88, 19 x 77 mm, aR, BS

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	25ET
UPC	051712831109
EAN	5027590470131
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	38.4 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	UL Recognized IEC Rated
GLOBAL CATALOG	25ET
PRODUCT TYPE	High speed british standard fuse

Powering Business Worldwide

Product specifications

AMPERAGE RATING	25 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
CLEARING (I2T)	150
WATT LOSSES	7 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	25
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf Bussmann series complete full line catalog no. 1007
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250044en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-8-80a-et.stp
TECHNICAL DATA SHEETS	720024 CT, ET, FE, EET, FEE, FM, FMM, MT, MMT fuses

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.