
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.- .
© COPYRIGHT – BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	O	TRANSFERED TO TYCO FORMAT	10JUL02	MF	EH




1 CRIMPBAND MATERIAL PROVIDED IN CONTINUOUS STRIP.

2 REFERENCE DESCRIPTIVE PART NUMBER L061/076C16B.

3 BLANK LENGTH DETERMINED BY 061/076 TOOLSET.



PARTIAL FORMED VIEW (REF)
FORMED BY APPLICATION TOOLING



TYP. CROSS SECTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± .005
4 PLC	± –
ANGLES	± –

MATERIAL: UNS C26000 BRASS –

FINISH: NONE

DWN	10JUL2002 MICHAEL S. FEHER
CHK	10JUL2002 EDWARD HOWARD
APVD	10JUL2002 EDWARD HOWARD
PRODUCT SPEC	–
APPLICATION SPEC	–
WEIGHT	–

tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105–3608

NAME
–
CRIMPBAND, RTM
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1601597	–

CUSTOMER DRAWING

SCALE 1:1 SHEET 1 OF 1 REV O

1601597–1
PART NUMBER

H:\