









RoHS
Compliant




REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

- 1) MATERIAL:
HOUSING: LCP S475 UL 94V-0
CONTACT: C5191
SHELL: SUS304-H
- 2) FINISH:
CONTACT: GOLD FLASH PLATED ON CONTACT AREA;
GOLD FLASH PLATED ON SOLDER TAILS,
- 3) ELECTRICAL CHARACTERISTICS
RATING CURRENT : 0.5A MAX.
CONTACT RESISTANCE : 50 mΩ MAX
DIELECTRIC WITHSTANDING : 500V AC MIN.
INSULATION RESISTANCE: 1000 MΩ MIN.
- 4) MECHANICAL CHARACTERISTICS
MATING CYCLE : 3000 CYCLES



SIM pin Assignment

PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司			
.X ±0.30	.X° ± 1°					
.XX ±0.10	.XX° ± 0.5°	MAT'L /	TITLE: MICRO SIM 1.35H 7P自弹卡座			
.XXX ± 0.05						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH /	MICRO SIM-7P-H1.35-30219		DWG NO.:	
		Q'TY /	CHKD:			
			DR:			
					SCALE	
			1/1		1/1	A