




NOTES:

1. MATERIAL:

- 1.1. HOUSING: PA ,COLOR IS BLACK;
- 1.2. CONTACT: PHOSPHOR COPPER ;

2. ELECTRICAL:

- 2.1. VOLTAGE RATING: 30 VAC RMS;
- 2.2. CURRENT RATING: 0.5 AMP;
- 2.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
- 2.4. WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
- 2.5. INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;

3. MECHANICAL:

- 3.1. MATING FORCE: 5~25N;
- 3.2. UNMATING FORCE: 5~25N;
- 3.3. OPERATING LIFE: 5000 CYCLES;

4. PLATING:

- 4.1. TERMINAL:
NI PLATING OVER ALL,
TIN PLATING ON SOLDER AREA,

5. ENVIRONMENTAL:

- 5.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
- 5.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;
- 6.SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

电气性能

序号	品名	材质	电镀/颜色	备注
A	底座	PA	黑色	
B	端子	H62	镀锡 镀锡	

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核				
			X. XX	±0.20	批 准				
			X. XXX	±0.10	APPROVAL				
			Angle	±3.0°	比 例				
					SCALE				
					投 影				
					Projection				
1	初版发行	日期				产品名称	325C 耳机插座 插件 黑色	版本	A
序号	变更内容	日期				TITLE		REV.	
No.	MODIFY CONTENT	MODIFY DATE				PART NO.	HC-PJ-325C-5P	UNITS	mm
						材料		SHEET	1/1
						MATERIAL			