




- 1.ROCKER SWITCH MODEL NO.SS21-BBHWG2-S2-R(0.5mm)
- 2.QUICK CONNECTOR TYPE;SINGLE POLE SINGLE THROW
- 3.RATING:10A 125/250VAC(C-UL)
12(4)A 250V~T85/55(ENEC17;NEMKO;CQC)


- 4.ACTUATOR COLOR:BLACK
- 5.HOUSING COLOR:BLACK
- 6.ACTUATOR PRINTING:" ON " "OFF" "WHITE COLOR

- 7.SILVER CONTACT:Ag ALLOY(t=0.5mm) CLAD COPPER ALLOY
- 8.ALL MATERIALS ARE ROHS COMPLIANT


TEL: 0769-82310511-867



PANEL CUTOUT DIMENSION



PANEL THICKNESS	X	Y
0.75~1.25mm	19.2 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm
1.25~2.0mm	19.4 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm
2.0~3.0mm	19.8 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2020.11.14	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10					SS21-BBHWG2-S2-R(0.5mm)		WIF121033	A1
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.							