

1.Description

The ESD5305FB is a low capacitance TVS (Transient Voltage Suppressor) array designed to protect high speed data interfaces. It has been specifically designed to protect sensitive electronic components which are connected to data and transmission lines from over-stress caused by ESD (Electrostatic Discharge).


3.Features

- Low capacitance:
 $C_{I/O-GND}=0.65\text{pF}$ typ. ($V_{DD}=\text{floated}$)
 $C_{I/O-GND}=0.35\text{pF}$ typ. ($V_{DD}=5\text{V}$)
- Ultra-low leakage current: $I_R<1\text{nA}$ typ.
- Solid-state silicon technology
- Low clamping voltage:
 $V_{CL}=12.8\text{V}$ @ $I_{PP}=16\text{A}$ (TLP)

2.Applications

- USB 2.0
- HDMI 1.3
- SATA and eSATA
- IEEE 1394
- PCI Express
- Portable Electronics
- Notebooks
- Reverse stand-off voltage: 5V max.
- Transient protection for each line according to IEC61000-4-2 (ESD): $\pm 30\text{kV}$ (contact discharge)
IEC61000-4-5 (surge): 6A (8/20 μs)

4.Pinning information




SOT23-6



5. Absolute Maximum Ratings $T_A = 25^\circ\text{C}$

Parameter	Symbol	Maximum	Units
Peak Pulse Power (8/20 μs)	P_{pk}	84	W
Peak Pulse Current (8/20 μs)	I_{pp}	6	A
ESD according to IEC61000-4-2 air discharge	V_{ESD}	± 30	kV
ESD according to IEC61000-4-2 contact discharge		± 30	kV
Junction temperature	T_J	125	$^\circ\text{C}$
Operation temperature	T_{OP}	-40 to 85	$^\circ\text{C}$
Storage temperature	T_{STG}	-55 to 150	$^\circ\text{C}$
Lead temperature	T_L	260	$^\circ\text{C}$



Definitions of electrical characteristics



6. Electrical Characteristic ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse stand-off voltage	V_{RWM}				5	V
Reverse leakage current	I_R	$V_{RWM}=5\text{V}$		<1	50	nA
Reverse breakdown voltage	V_{BR}	$I_{BR}=1\text{mA}$	7	8	9	V
Forward voltage	V_F	$I_F=10\text{mA}$	0.6	0.9	1.2	V
Clamping voltage ¹⁾	V_{CL}	$I_{PP}=16\text{A}$, $t_p=100\text{ns}$		12.8		V
Dynamic resistance ¹⁾	R_{DYN}			0.24		Ω
Clamping voltage ²⁾	V_{CL}	$I_{PP}=1\text{A}$, $t_p=8/20\mu\text{s}$			10	V
		$I_{PP}=6\text{A}$, $t_p=8/20\mu\text{s}$			14	V
	$C_{I/O - GND}$	$V_R=0\text{V}$, $f=1\text{MHz}$ $V_{DD}=\text{floated}$, any I/O to GND		0.65	1	pF
		$V_R=0\text{V}$, $f=1\text{MHz}$ $V_{DD}=5\text{V}$, any I/O to GND		0.35	0.5	pF
	$C_{I/O - I/O}$	$V_R=0\text{V}$, $f=1\text{MHz}$, any I/O to I/O		0.35	0.5	pF


Notes:

1) TLP parameter: $Z_0=50\Omega$, $t_p=100\text{ns}$, $t_r=2\text{ns}$, averaging window from 60ns to 80ns. R_{DYN} is calculated from 10A to 30A.

2) Non-repetitive current pulse, according to IEC61000-4-5.




7.1Typical characteristic






7.2Typical characteristic





8.SOT-23-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



9.Ordering Information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW ESD5305FB	SOT23-6	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.