










Specifications


- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω

X3025 W V X-2x06 -46SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Series No.
② Category : W-WAFER
③ Welding Board Angle : V-Straight 180°
④ Welding Way: Blank-DIP
⑤ Row No.-Pin No.: 2*XX-2*01P~2*22P
⑥ Plug the Pin & Special No.:
⑦ Material: 66-PA66 94V-0 ;PT-PBT 94V-0;
46-PA46 94V-0 LP-LCP 94V-0
⑧ Plating Category: SN-Bright Tin Plating;
V01-All Gold Flash
⑨ Color : Blank-Natural Color







Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	---	6.65	2*07	18.00	24.65
2*02	3.00	9.65	2*08	21.00	27.65
2*03	6.00	12.65	2*09	24.00	30.65
2*04	9.00	15.65	2*10	27.00	33.65
2*05	12.00	18.65	2*11	30.00	36.65
2*06	15.00	21.65	2*12	33.00	39.65

PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing
X3025 WV-2x06-46V01	PA 46 UL 94V-0	Brass	Gold- Flash	X3025H
X3025WV-2x06-LPSN	LCP UL 94V-0		Tin-Plated	
X025 WV-2x06-66]SN	PA 66 UL 94V-0			
X3025 WV-2x06-46SN	PA 46 UL 94V-0			
X3025WV-2x06-PTSN	PBT UL 94V-0			

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				XKB
ΔX				
ΔX				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤4	±0.2
4<L≤16	±0.3
16<L≤63	±0.4
L>63	±0.5

www.helloxkb.com

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X3025WV- 2x06-46SN
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025WV- 2x06-46SN
APPD		DATE		SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
1.0g	1/1	A0