RS1501M THRU RS1507M
6GBJ Plastic-Encapsulate Bridge Rectifier

Reverse Voltage
50-1000 V


Forward Current
15.0 A max

Features
- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Reliable low cost construction utilizing molded plastic technique

Applications
- General purpose use in AC/DC bridge full wave rectification

Mechanical Data
- Case：6GBJ
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant,Solder plated, solderable per MIL-STD-750,Method 2026

Appearance Image



Marking
- RS15xxM(1~7)

Maximum Ratings @ Ta = 25℃ unless otherwise noted

PARAMETER	SYMBOL	UNIT	RS1501M	RS1502M	RS1503M	RS1504M	RS1505M	RS1506M	RS1507M
Repetitive peak reverse voltage	V_{RRM}	V	100	200	400	600	800	1000	1200
Maximum RMS voltage	V_{RMS}	V	70	140	280	420	560	700	840
Maximum DC blocking Voltage	V_{DC}	V	100	200	400	600	800	1000	1200
Maximum average output current@60Hz sine wave, resistance load	$I_{F(AV)}$	A	15.0						
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I_{FSM}	A	250						
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	500						
Current squared time @1ms≤t<8.3ms Tj=25℃，Rating of per diode	I^2t	A^2S	259.38						
Storage temperature	T_{stg}	℃	-55～+150						
Junction temperature	T_j	℃	-55～+150						

Electrical Characteristics @ Ta = 25℃ unless otherwise noted

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	RS1501M	RS1502M	RS1503M	RS1504M	RS1505M	RS1506M	RS1507M
Maximum instantaneous forward voltage	I_F=7.5A	V_F	V	1.0						
Maximum DC reverse currentat rated DC blocking voltage	V_R=V_{DC}, Tj=25℃	I_R	μA	10						
	V_R=V_{DC}, Tj=100℃	I_R		500						

Characteristic Curve (Typical)




FIG1.Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3.Typical Forward Characteristics





FIG4.Typical Reverse Characteristics


Marking and packet information



RS15M**：Marking Model　　**TOS**：Brand Logo

Packaging information	
每盒	250PCS
每箱	2000PCS
脚长定制	支持

6GBJ Package outline dimensions



Dimensions in milimeters

Notice

XILONG reserves the right to make modifications,enhancements,improvements,corrections or other changes without further notice to any product herein.
xilong does not assume any liability arising out of the application or use of any product described herein.