

321017 ✓ ACTIVE




PIDG

TE Internal #: 321017

Closed Ring Tongue Terminal, 26 – 22 AWG, #4 / M2.5 Stud, 3.02 mm [.119 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: M2.5, #4

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.232 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method	Box
------------------	-----

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
----------------------------	-----------------------------



Stud Size	M2.5, #4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	3.02 mm [.119 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	16.41 mm [.646 in]
Compatible Insulation Diameter (Max)	2.03 mm [.08 in]
Compatible Insulation Diameter Range	1.27 – 2.03 mm [.05 – .08 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900

	ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY



TE Part # 46121
DAHT PG PIDG 26-22 ASSY


Also in the Series | PIDG




Compression Connectors(17)




Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)




Knife Disconnects(11)




Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)






Special Purpose Terminals(1)



Splices(41)

Customers Also Bought

TE Part #CAT-C8114-EJ79
IEC Filtered Inlets, Corcom EJT SeriesTE Part #2-1617109-6
PRMAC-12X = COTS T05TE Part #1676402-2
RN 0805 64K9 0.1% 10PPM 1KRLTE Part #CTJ112E01E-513
MODULE ASSYTE Part #2-320563-4
TERMINAL,PIDG R IR 14 1/4TE Part #CTD160E01F
MODULE ASSYTE Part #CTJ-3A-04-4021
RAIL ASSYTE Part #3-1617108-2
PRMAC-26X=PRMA COTS TO-5 RELAYTE Part #582853-000
382A034-15-CS-2067-0

Documents

Product Drawings

[TERMINAL,PIDG R 26-22 4](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_321017_T.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_321017_T.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_321017_T.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_321017_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_321017_N.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_321017_N.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English