
926329-1 ✔ ACTIVE

AMP-LATCH

TE Internal #: 926329-1

TE Internal Description: KEYING PLUG

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1-926209-0
2X10P LOCK-CLIP GEH




TE Part # 926657-9
9P LOCKG CLIP GEH




TE Part # 926209-7
2X7P LOCK-CLIP GEH




TE Part # 926209-4
2X4P LOCK-CLIP GEH



TE Part # 926657-8
LOCKING CLIP HSG



TE Part # 926657-6
LOCKING CLIP HSG




TE Part # 926657-7
7P LOCKG CLIP GEH



TE Part # 926209-8
2X8P LOCK-CLIP GEH




TE Part # 926209-6
2X6P LOCK-CLIP GEH




TE Part # 926657-5
5P LOCKG CLIP GEH



TE Part # 926209-5
LOCKING CLIP HSG.



TE Part # 926657-4
LOCKING CLIP HSG



TE Part # 926657-3
3P LOCKG CLIP GEH




TE Part # 965082-1
2X 2P LOCK-CLIP GEH



TE Part # 5-926657-4
4P LOCK-CLIP GEH



TE Part # 1-926657-2
12P LOCKG CLIP GEH



TE Part # 1-926657-3
13P LOCKG CLIP GEH



TE Part # 1-926657-1
11P LOCKG CLIP GEH



TE Part # 1-926657-5
15P LOCKG CLIP GEH



TE Part # 1-926657-0
10P LOCKG

Customers Also Bought



TE Part #1-6609031-7
20ER1=F7193 S0




TE Part #4-1609153-9
PS0S0DM6E=C7093



TE Part #104503-4
05 MTE PIN HSG SR RIB .100CL



TE Part #4-6609951-0
PS0SXDH6B=C4454



TE Part #926657-5
5P LOCKG CLIP GEH



TE Part #926209-8
2X8P LOCK-CLIP GEH



TE Part #5677964005
RNF-3000-39/13-X-SP



TE Part #7574442007
RAYRIM-NR8-0-STK



TE Part #5-1768045-8
STD15W-BLANK

TE Part #2-1393560-1
V42254A 132V 1=SUB D BOLZENSA

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_926329-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_926329-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_926329-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.