EH3264-000 ✔ ACTIVE

RAYCHEM

TE Internal #: EH3264-000

Black, 2:1, Single Wall Tubing, Shrinks To 4 mm [.157 in], Elastomer, Expanded Inside 8 mm [.315 in], Highly Flame-Retardant, Spool, -75 – 150 °C

View on TE.com >

Heat Shrink Tubing > Single Wall ZH 150: Heat Shrink Tubing, 2:1 Shrink Ratio



Primary Product Color: **Black**

Shrink Ratio: **2:1**

Wall Type: **Single Wall**

Recovered Inside Diameter (Max): **4 mm [.157 in]**

Primary Product Material: **Elastomer**

All Single Wall ZH 150: Heat Shrink Tubing, 2:1 Shrink Ratio (8)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Body Features

Material Systems Code	25, 100
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Elastomer
Flexibility	Flexible

Dimensions

Recovered Inside Diameter (Max)	4 mm[.157 in]
Expanded Inside Diameter (Min)	8 mm[.315 in]
Tubing Size Range	4 – 8 mm[.157 – .315 in]

Usage Conditions

Tubing Flammability Type	Highly Flame-Retardant
Operating Temperature Range	-75 – 150 °C
Recovery Temperature	175 °C

Packaging Features

Packaging Method	Spool

Operation/Application

Mechanical Resistance	Fluids

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Customers Also Bought



TE Part #D42180-000
B-155-05



TE Part #1-1478904-0
SMA STR PLG DS RG405 GSS




TE Part #CB5429-000
XFFR-03X25




TE Part #51863-3
TERM,RING, PIDG, IR, 20, #6

TE Part #EH3268-000
ZH150-24/12-0-SP



TE Part #A70754-000
B-155-03



TE Part #6661533001
100G0111-3.00-2

TE Part #BAB0258-00
BTH1-11-06-4-C

TE Part #EK6791-000
PC4B0031-19N-1-B

TE Part #PC4F0020-19NX-1-B
PC4F0020-19NX-1-B

Documents

Product Drawings

ZH150-8/4-0-SP

English

Datasheets & Catalog Pages

1654025_Sec3_ZH-100

English

raychem-tubing-product-selection-guide

English

Product Specifications

Installation instructions for ZH150 tubing

English