

1. Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $R_{DS(ON)}$, fast switching speed and extremely low $R_{DS(ON)}$ in a small package.


2. Features

- $V_{DS(V)}=30V$
- $R_{DS(ON)}=8m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}=10m\Omega(V_{GS}=4.5V)$
- Low gate charge
- Fast Switching
- High performance trench technology for extremely low $R_{DS(ON)}$

3. Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



4. Absolute Maximum Ratings $T_A=25^\circ C$

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DSS}	30	V
Gate-Source Voltage	V_{GSS}	± 20	
Continuous Drain Current	I_D	@ $T_C=25^\circ C$ (Note 3)	66
		@ $T_A=25^\circ C$ (Note 1a)	15
		Pulsed (Note 1a)	100
Power Dissipation	P_D	@ $T_C=25^\circ C$ (Note 3)	63
		@ $T_A=25^\circ C$ (Note 1a)	3.2
		@ $T_A=25^\circ C$ (Note 1b)	1.3
Storage Junction Temperature Range	T_J, T_{STG}	-55 to 175	$^\circ C$



5. Thermal Characteristics

Parameter		Symbol	Rating	Units
Thermal Resistance, Junction-to-Case	(Note 1)	$R_{\theta JC}$	2.4	$^{\circ}\text{C/W}$
Thermal Resistance, Junction-to-Ambient	(Note 1a)	$R_{\theta JA}$	40	$^{\circ}\text{C/W}$
Thermal Resistance, Junction-to-Ambient	(Note 1b)	$R_{\theta JA}$	96	$^{\circ}\text{C/W}$



6. Electrical Characteristic ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Avalanche Energy	E_{AS}	Single Pulse, $V_{DD}=15\text{V}$, $I_D=66\text{A}$			67	mJ
Drain-Source Avalanche Current	I_{AS}				66	A
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0\text{V}$, $I_D=250\mu\text{A}$	30			V
Breakdown Voltage Temperature Coefficient	$\frac{\Delta BV_{DSS}}{\Delta T_J}$	$I_D=250\mu\text{A}$ Referenced to 25°C		26		mV/ $^\circ\text{C}$
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=24\text{V}$, $V_{GS}=0\text{V}$			1	μA
Gate-Body Leakage	I_{GSS}	$V_{GS}=\pm 20\text{V}$, $V_{DS}=0\text{V}$			± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_D=250\mu\text{A}$	1	1.8	3	V
Gate Threshold Voltage Temperature Coefficient	$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	$I_D=250\mu\text{A}$ Referenced to 25°C		-5		mV/ $^\circ\text{C}$
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS}=10\text{V}$, $I_D=15\text{A}$ $V_{GS}=4.5\text{V}$, $I_D=13\text{A}$		6.3 7.9	8 10	m Ω m Ω
On-State Drain Current	$I_{D(on)}$	$V_{GS}=10\text{V}$, $V_{DS}=5\text{V}$	50			A
Forward Transconductance	g_{FS}	$V_{DS}=10\text{V}$, $I_D=15\text{A}$		60		S
Input Capacitance	C_{iss}	$V_{DS}=15\text{V}$, $V_{GS}=0\text{V}$, $f=1\text{MHz}$		1755		pF
Output Capacitance	C_{oss}			430		pF
Reverse Transfer Capacitance	C_{rss}			180		pF
Gate Resistance	R_g	$V_{OSC}=15\text{mV}$, $f=1\text{MHz}$		1.3		ns
Turn-On Delay Time	$t_{D(on)}$	$V_{DD}=15\text{V}$, $I_D=1\text{A}$ $V_{GS}=10\text{V}$, $R_{GEN}=6\Omega$		11	20	ns
Turn-On Rise Time	t_r			12	21	ns
Turn-Off Delay Time	$t_{D(off)}$			29	47	ns
Turn-Off Fall Time	t_f			19	34	ns
Total Gate Charge	Q_g	$V_{DS}=15\text{V}$, $I_D=15\text{A}$		16	22	nC
Gate-Source Charge	Q_{gs}	$V_{GS}=5\text{V}$		4.6		nC
Gate-Drain Charge	Q_{gd}			6.2		nC



Maximum Continuous Drain–Source Diode Forward Current	I_S				2.3	A
Drain–Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=2.3A$ (Note 2)		0.74	1.2	V
Diode Reverse Recovery Time	t_{rr}	$I_F=15A, dI_F/dt=100A/\mu s$		28		ns
Diode Reverse Recovery Charge	Q_{rr}			18		nC

Notes:

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.

$R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



■ a) $R_{\theta JA}=45^{\circ}C/W$ when mounted on a 1in² pad of 2oz copper.



■ b) $R_{\theta JA}= 96^{\circ}C/W$ when mounted on a minimum pad.

Scale 1 : 1 on letter size paper.







2. Pulse Test: Pulse Width < 300μs, Duty Cycle < 2.0%.

3. Maximum current is calculated as: $\sqrt{\frac{P_D}{R_{DS(ON)}}}$

where P_D is maximum power dissipation at $T_C=25^{\circ}C$ and $R_{DS(ON)}$ is at $T_{J(max)}$ and $V_{GS}=10V$. Package current limitation is 21A.




7.1 Typical characteristic

 <p style="text-align: center;">I_D, Drain-Source Current (A)</p> <p style="text-align: center;">V_{DS}, Drain To Source Voltage (V)</p>	 <p style="text-align: center;">$R_{DS(ON)}$, Normalized Drain-Source On-Resistance</p> <p style="text-align: center;">I_D, Drain Current (A)</p>
<p style="text-align: center;">Figure 1: On-Region Characteristics</p>	<p style="text-align: center;">Figure 2: On-Resistance Variation with Drain Current and Gate Voltage</p>
 <p style="text-align: center;">$R_{DS(ON)}$, Normalized Drain-source On-resistance</p> <p style="text-align: center;">T_J, Junction Temperature (°C)</p>	 <p style="text-align: center;">$R_{DS(ON)}$, On-Resistance(OHM)</p> <p style="text-align: center;">V_{GS}, Gate To Source Voltage (V)</p>
<p style="text-align: center;">Figure 3: On-Resistance Variation with Temperature</p>	<p style="text-align: center;">Figure 4: On-Resistance Variation with Gate-to-Source Voltage</p>
 <p style="text-align: center;">I_D, Drain Current (A)</p> <p style="text-align: center;">V_{GS}, Gate To Source Voltage (V)</p>	 <p style="text-align: center;">I_S, Reverse Drain Current (A)</p> <p style="text-align: center;">V_{SD}, Body Diode Forward Voltage (V)</p>
<p style="text-align: center;">Figure 5: Transfer Characteristics</p>	<p style="text-align: center;">Figure 6: . Body Diode Forward Voltage Variation with Source Current and Temperature</p>




7.2 Typical characteristic





8.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38	BSC	1.27	1.90	1.00	8.00



9. Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW FDD6670A	TO-252	2500	Tape and reel



10. Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.