








Specifications:

规格:

Voltage rating:350V AC/DC

额定电压: 350V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X1501 H - 2x12 - N0

① ② ③ ④

1.Series No

2.Category:H-Housing

3.Row No.Pin No:2xXX-2x05~2x20 Pin

4.Material:N0-PA66 UL 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x05	7.50	6.00	11.20	2x11	16.50	15.00	20.20
2x06	9.00	7.50	12.70	2x12	18.00	16.50	21.70
2x07	10.50	9.00	14.20	2x13	19.50	18.00	23.20
2x08	12.00	10.50	15.70	2x14	21.00	19.50	24.70
2x09	13.50	12.00	17.20	2x15	22.50	21.00	26.20
2x10	15.00	13.50	18.70	2x20	30.00	28.50	33.70

X1501H-2x12-N0	PA66	X1501W	X1501T
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X1501H-2x12-N0
CHKD		UNIT: mm/in	DWG NO.: X-X1501H-2x12-N0
APPD		SIZE: A4	

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0