T1619101220-000 ✔ ACTIVE

HDC | HDC IP65

TE Internal #: T1619101220-000

Heavy Duty Connector Base Housing, Side Entry, Locking, Sealable, HDC IP65

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Features

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Cable Entry Location	Side

Mechanical Attachment

Locking Device Location	Housing
Thread Size	2M20
Hood & Base Locking Device Type	Locking

Housing Features

Housing Material	Die Cast Aluminum

Dimensions

Product Height	57 mm

Usage Conditions

Corrosion Protected	Yes

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # T2010102201-000
HA-010-F



TE Part # T3609200102-000
DLX-20-M



TE Part # T1319100125-000
H10A-TS-M25



TE Part # T1319100220-000
H10A-TS-2M20

Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases (1258)

Customers Also Bought



TE Part #T2070064001-000
H6BN-T2



TE Part #2350890-1
20POS,HYBRID,SOC HSG ASSY,SLD, COD A



TE Part #T1620243125-000
H24B-SDR-LB-M25



TE Part #2350891-1
20POS,HYBRID,PIN HSG ASSY,SLD, COD A



TE Part #T1019161201-001
H16A-KDTMS



TE Part #T1470102121-000
H10B-SGRH-PG21



TE Part #T2080072101-000
HQ-007-M



TE Part #T3209111201-000
HSK-P11G



TE Part #T3209201222-001
HSK-M20G

Documents

Product Drawings

H10A-SGRS-2M20

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1619101220-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1619101220-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1619101220-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification