

Features

- Operate From 1.65V to 5.5V
- 5 V tolerant input/output for interfacing with 5 V logic
- $\pm 24\text{mA}$ output drive ($V_{CC} = 3.3\text{V}$)
- CMOS low-power consumption and high noise immunity
- OFF Supports Partial-Power-Down Mode Operation
- Latch-up performance exceeds 100mA
- Specified from -40°C to $+125^\circ\text{C}$
- SOT23-6 Package Available
- SOT363 Package Available


General Description

The SN74LVC2G17 is a high-performance, low-power, low-voltage, Si-gate CMOS device which provides two independent buffers with Schmitt trigger action. It is capable of transforming slowly changed input signals into sharply defined, jitter-free output signals.


Ordering Information

ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION
SN74LVC2G17DBVR	SOT23-6	Tape and Reel,3000
SN74LVC2G17DCKR	SOT363	Tape and Reel,3000

Logic Diagram



Pin Configuration



Function Table

INPUT(A)	OUTPUT(Y)
L	L
H	H

H=High Level

L=Low Level

Applications

- Voltage Level Shifting
- General Purpose Logic
- Power Down Signal Isolation
- Wide array of products such as:
 - PCs, Networking, Notebooks, Netbooks, PDAs
 - Tablet Computers, E-readers
 - Computer Peripherals, Hard Drives, CD/DVD ROM
 - TV, DVD, DVR, Set-Top Box
 - Cell Phones, Personal Navigation / GPS
 - MP3 Players, Cameras, Video Recorders

Marking

SN74LVC2G17DBVR Marking:C17R

SN74LVC2G17DCKR Marking:C7R

Absolute Maximum Ratings

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V_{CC}	-0.5 ~ 6.5	V
Input Voltage (Note 2)	V_{IN}	-0.5 ~ 6.5	V
Output Voltage (Note 2,3)	High-Impedance	-0.5 ~ 6.5	V
	Power-Off State		
	High State	-0.5 ~ $V_{CC}+0.5$	V
	Low State		
Input Clamp Current ($V_{IN}<0$)	I_{IK}	-50	mA
Output Clamp Current ($V_{OUT}<0$)	I_{OK}	-50	mA
Output Current	I_{OUT}	± 50	mA
V_{CC} or GND Current	I_{CC}	± 100	mA
Junction Temperature	T_J	+150	°C
Storage Temperature	T_{STG}	-65 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

3. The value of V_{CC} is provided in the recommended operating conditions table.

Recommended Operating Conditions

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	V_{CC}	Operating	1.65		5.5	V
Input Voltage	V_{IN}		0		5.5	V
Output Voltage	V_{OUT}	High or low state	0		V_{CC}	V
High-Level Input Voltage	V_{T+}	$V_{CC} = 1.65\text{ V}$	0.70		1.40	V
		$V_{CC} = 2.3\text{ V}$	1.00		1.70	V
		$V_{CC} = 3.0\text{ V}$	1.30		2.20	V
		$V_{CC} = 4.5\text{ V}$	1.90		3.10	V
		$V_{CC} = 5.5\text{ V}$	2.20		3.70	V
Low-Level Input Voltage	V_{T-}	$V_{CC} = 1.65\text{ V}$	0.30		0.70	V
		$V_{CC} = 2.3\text{ V}$	0.40		1.00	V
		$V_{CC} = 3.0\text{ V}$	0.60		1.30	V
		$V_{CC} = 4.5\text{ V}$	1.10		2.00	V
		$V_{CC} = 5.5\text{ V}$	1.40		2.50	V
Hysteresis Voltage	ΔV_T	$V_{CC} = 1.65\text{ V}$	0.30		0.80	V
		$V_{CC} = 2.3\text{ V}$	0.40		0.90	V
		$V_{CC} = 3.0\text{ V}$	0.40		1.10	V
		$V_{CC} = 4.5\text{ V}$	0.60		1.30	V
		$V_{CC} = 5.5\text{ V}$	0.70		1.40	V
Operating Temperature	T_A		-40		+125	°C

Note: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation.

Electrical Characteristics ($T_A = 25^\circ\text{C}$, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
High-Level Output Voltage	V_{OH}	$V_{CC}=1.65\text{V}\sim 5.5\text{V}$, $I_{OH}=-100\mu\text{A}$	$V_{CC}-0.1$			V
		$V_{CC}=1.65\text{V}$, $I_{OH}=-4\text{mA}$	1.20			V
		$V_{CC}=2.3\text{V}$, $I_{OH}=-8\text{mA}$	1.90			V
		$V_{CC}=3.0\text{V}$, $I_{OH}=-16\text{mA}$	2.40			V
		$V_{CC}=3.0\text{V}$, $I_{OH}=-24\text{mA}$	2.30			V
		$V_{CC}=4.5\text{V}$, $I_{OH}=-32\text{mA}$	3.80			V
Low-Level Output Voltage	V_{OL}	$V_{CC}=1.65\sim 5.5\text{V}$, $I_{OL}=100\mu\text{A}$			0.10	V
		$V_{CC}=1.65\text{V}$, $I_{OL}=4\text{mA}$			0.45	V
		$V_{CC}=2.3\text{V}$, $I_{OL}=8\text{mA}$			0.30	V
		$V_{CC}=3.0\text{V}$, $I_{OL}=16\text{mA}$			0.40	V
		$V_{CC}=3.0\text{V}$, $I_{OL}=24\text{mA}$			0.55	V
		$V_{CC}=4.5\text{V}$, $I_{OL}=32\text{mA}$			0.55	V
Input Leakage Current	$I_{I(LEAK)}$	$V_{IN}=0$ to 5.5V , $V_{CC}=0\sim 5.5\text{V}$			± 5	μA
Power OFF Leakage Current	I_{OFF}	V_{IN} or $V_{OUT}=5.5\text{V}$, $V_{CC}=0$			± 10	μA
Quiescent Supply Current	I_{CC}	$V_{IN}=V_{CC}$ or GND, $I_{OUT}=0$ $V_{CC}=1.65\sim 5.5\text{V}$			10	μA
Additional Quiescent Supply Current	ΔI_{CC}	One input at $V_{CC}-0.6\text{V}$ Other inputs at V_{CC} or GND, $I_{OUT}=0$, $V_{CC}=3\sim 5.5\text{V}$			500	μA
Input Capacitance	C_I	$V_{IN}=V_{CC}$ or GND, $V_{CC}=3.3\text{V}$		4		pF

Switching Characteristics ($T_A = 25^\circ\text{C}$, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Propagation delay nA to nY	t_{PLH} t_{PHL}	$V_{CC}=1.8\text{V}\pm 0.15\text{V}$, $C_L=30\text{pF}$, $R_L=1\text{K}\Omega$	3.9		9.3	ns
		$V_{CC}=2.5\text{V}\pm 0.2\text{V}$, $C_L=30\text{pF}$, $R_L=500\Omega$	1.9		5.7	ns
		$V_{CC}=3.3\text{V}\pm 0.3\text{V}$, $C_L=50\text{pF}$, $R_L=500\Omega$	2.2		5.4	ns
		$V_{CC}=5\text{V}\pm 0.5\text{V}$, $C_L=50\text{pF}$, $R_L=500\Omega$	1.5		4.3	ns

Operating Characteristics (Unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Power Dissipation Capacitance	C_{PD}	$V_{CC}=5\text{V}$, $f=10\text{MHz}$		21		pF


Package Outline Dimensions (Unit: mm)

SOT23-6




Dimension	Min.	Max.
A	2.80	3.00
B	1.50	1.70
C	1.00	1.20
D	0.35	0.45
E	0.35	0.55
G	0.90	1.00
H	0.02	0.10
J	0.10	0.20
K	2.60	3.00

Mounting Pad Layout (Unit: mm)



Package Outline Dimensions (Unit: mm)

SOT363



Dimension	Min.	Max.
A	2.00	2.20
B	1.15	1.35
C	0.85	1.05
D	0.15	0.35
E	0.25	0.40
G	0.60	0.70
H	0.02	0.10
J	0.05	0.15
K	2.20	2.40

Mounting Pad Layout (Unit: mm)

