




## 陶瓷气体放电管 Ceramic Gas Discharge Tube



目录编号 Catalog No.	直流击穿电压 DC Spark Over Voltage (100v/s) V	冲击击穿电压 Impulse Spark Over Voltage (1kv/μs) V	绝缘电阻 Insulation Resistance GΩ	极间电容 Electrode Capacitance 1MHz 0.5V PF	耐短波电流 Impulse Discharge Current (8/20μs 10 times)	耐交流电流 AC Discharge Current (50Hz 1s 10 times) A
5TS075L	075±20%	≤600	≥1	≤1.5	5KA	5A
5TS090L	090±20%	≤600	≥1	≤1.5	5KA	5A
5TS150L	150±20%	≤600	≥1	≤1.5	5KA	5A
5TS230L	230±20%	≤700	≥1	≤1.5	5KA	5A
5TS350L	350±20%	≤1000	≥1	≤1.5	5KA	5A
5TS420L	420±20%	≤1000	≥1	≤1.5	5KA	5A
5TS470L	470±20%	≤1200	≥1	≤1.5	5KA	5A
5TS600L	600±20%	≤1400	≥1	≤1.5	5KA	5A
5TS800L	800±20%	≤1600	≥1	≤1.5	5KA	5A

- 参考执行标准: ITU-T K.12, GB/T9043-2008 《通信设备过电压保护用气体放电管通用技术条件》。  
Reference executive standard: ITU-T K.12, GB/T9043-2008 《General Technical Requirements of Gas Discharge Tubes for the Over-voltage protection of telecommunications installations》.
- 耐交流 ( 50 Hz ) 电流最大 5A, 试验时交流电压应大于直流击穿电压上限值。  
The maximum AC withstand current (50 Hz) is 5 A and AC voltage shall be larger than the upper limit value of DC spark-over voltage during the test.
- 极间电容测试频率为1MHz, 测试电压为0.5V。  
The electrode capacitance test frequency is 1MHz and test voltage is 0.5V.

### 工作与储存温度 Operating and Storage temperature

-40°C ~ +85°C

### 包装 Packaging

产品采用吸塑盒包装, 100PCS/盒, 每包装箱装4000PCS  
Automaton taped 100PCS per reel, 4000PCS per carton