


压线端子

详情说明



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8	6
AMP.	9	12	17	18	30	35	50	70	95

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE	DIMENSION inch(mm)								QTY BOX
	BRAZED SEAM	BUTTED SEAM		d2	W	F	L	E	D	d1	T	
14-12 A.W.G.	<input type="checkbox"/>	<input type="checkbox"/>	#8	0.169	0.315	0.276	0.72	0.236	0.197	0.118	0.039	1000
2.5-4 mm ²	<input type="checkbox"/> SNB3-4	<input type="checkbox"/> SN3-4		4.3	8	7	18.3	6	5.000	3	1	
14-12 A.W.G.	<input type="checkbox"/>	<input type="checkbox"/>	#10	0.209	0.315	0.276	0.72	0.236	0.197	0.118	0.039	1000
2.5-4 mm ²	<input type="checkbox"/> SNB3-5	<input type="checkbox"/> SN3-5		5.3	8	7	18.3	6	5.000	3	1	
12-10 A.W.G.	<input type="checkbox"/>	<input type="checkbox"/>	#10	0.209	0.354	0.276	0.72	0.236	0.220	0.134	0.039	1000
4-6 mm ²	<input type="checkbox"/> SNB5-5	<input type="checkbox"/> SN5-5		5.3	9	7	18.3	6	5.600	3.4	1	