









P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB	REVISED PER ECN-25-331570	27JUN2025	TR	RK

NOTES:

- 1 TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15 .
- 2 CONTACT PLATING:
OVERALL: $\text{Ni } 1.27\mu\text{m MIN.}$ ALL OVER THE CONTACTS
SOLDER ZONE: $\text{Sn } 3.5\text{-}5.0\mu\text{m}$ ON THE SOLDER ZONE OF THE CONTACT
MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19117
- 3 MATERIALS:
HOUSING: 30% G.F. LCP COLOR BLACK, UL 94V-0.
CONTACTS: PHOSPHOR BRONZE
SOLDER BRACKET: TIN PLATED BRASS WITH NICKEL UNDERPLATE.
- 4 THIS JACK CAN ALSO BE APPLIED HANGING THROUGH A HOLE, IN A PRINTED CIRCUIT BOARD. SEE LEFT PCB LAYOUT.
- 5 SURFACE CAN BE USED FOR PICKING THE MODULAR JACK WITH, TYPE 11 SMD MACHINE.
- 6 MEASURED AT HEEL OF CONTACTS
COPLANARITY AT TIPS OF CONTACTS MAX. 0.18mm
- 7 TAPE AND REEL PACKAGING ACCORDING TO EIA 481-3 SPECIFICATIONS.
- 8 INCLUDES KAPTON TAPE (10x11,5mm) ON TOP SURFACE AS PICK AND PLACE FEATURE.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINSI



9	4 POS./4 CONT.	750 PCS ON $\varnothing 560$ mm OD REEL. BOTTOM ENTRY ORIENTATION PER DETAIL B2	2-338084-5
	4 POS./4 CONT.	750 PCS ON $\varnothing 560$ mm OD REEL. TOP ENTRY ORIENTATION PER DETAIL B1	2-338084-3
	4 POS./4 CONT.	300 PCS ON $\varnothing 360$ mm OD REEL. TOP ENTRY ORIENTATION PER DETAIL B1	8 1-338084-6
9	4 POS./4 CONT.	300 PCS ON $\varnothing 360$ mm OD REEL. BOTTOM ENTRY ORIENTATION PER DETAIL B2	1-338084-5
	4 POS./4 CONT.	300 PCS ON $\varnothing 360$ mm OD REEL. TOP ENTRY ORIENTATION PER DETAIL B1	1-338084-3
	REMARKS	PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC \pm
 1 PLC ± 0.1
 2 PLC ± 0.01
 3 PLC ± 0.001
 4 PLC ± 0.0001
 ANGLES \pm
 FINISH

MATERIAL: TBD SEE NOTE 3 material_2

FINISH: SEE NOTE 2 finish_spec_2

APVD: R. SMEETS
 CHK: E. STELLINGA
 DATE: 27 JUN 2025
 DEC. '96

NAME: INVERTIBLE MODULAR JACK, 4 POS HANDSET SURFACE MOUNT APPLICATION

SIZE: A2
 CAGE CODE: 0779
 DRAWING NO: C-338084
 RESTRICTED TO: -

WEIGHT: 1.92 gr




CUSTOMER DRAWING

SCALE: 5:1

SHEET 1 OF 2

REV AB


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



09 USER DIRECTION OF UNREELING

** INSPECTION NUMBER 19 POINTS: 01 - 19

18 9. MAXIMUM CAMBER



100975-3	585DIA-100DIA(HUB)-48.0W(36.0W INSIDE)	CORRUGATED	973053-6	780 POCKETS MIN	8-1533444-5	A	623105-7
100975-1	380DIA-100DIA(HUB)-38.4W(32.4W INSIDE)	PLASTIC	2-1533174-4	330 POCKETS MIN	8-1533444-5	A	623105-5
REPLACED PN	SIZE (REF.)	FLANGE MATERIAL	PART NUMBER	19 QUANTITY PER ROLL	PET TAPE	REV.	PN
REEL							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27 JUN 2025	TE Connectivity	
		CHK E. v. ELJK DEC. '96		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. SMEETS	NAME INVERTIBLE MODULAR JACK, 4 POS HANDSET SURFACE MOUNT APPLICATION	
0 PLC ±	1 PLC ±0.1	PRODUCT SPEC 108-19117	SIZE	CAGE CODE
2 PLC ±0.01	3 PLC ±0.001	APPLICATION SPEC 114-19041	DRAWING NO	RESTRICTED TO
4 PLC ±0.0001	ANGLES ±	WEIGHT 1.92 gr	A200779	C-338084
MATERIAL TBD	FINISH -	CUSTOMER DRAWING	SCALE 5:1	SHEET 2 OF 2
material_2	finish_spec_2			REV AB