


Features

- Low operating voltage: 5V
- Ultra low capacitance: 0.7pF
- Solid-state silicon-avalanche and active circuit triggering technology
- Back-drive protection for power-down mode
- Lead-free version available

IEC COMPATIBILITY (EN61000-4)

- IEC 61000-4-2 (ESD) $\pm 27\text{kV}$ (air), $\pm 16\text{kV}$ (contact)
- IEC 61000-4-4 (EFT) Level-3,55A (5/50ns)
- IEC 61000-4-5 (Lightning) 6A (8/20 μs)

**SOT-23-6L**


Mechanical Characteristics

- SOT-23-6L package
- Molding compound flammability rating: UL 94V-0
- Marking: Marking Code
- Packaging: Tape and Reel
- RoHS/WEEE Compliant


Applications

- Video/Graphics Card
- Digital Visual Interface (DVI)
- USB2.0 Power and Data lines protection
- Notebook and PC Computers
- Monitors and Flat Panel Displays

Circuit Diagram



Schematic & PIN Configuration




Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 8/20\mu s$)	P_{PP}	120	Watts
Peak Pulse Current ($t_p = 8/20\mu s$)	I_{PP}	6	A
Operating Temperature	T_J	-55 to + 85	°C
Storage Temperature	T_{STG}	-55 to +150	°C

Electrical Parameters (T=25°C)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F



Electrical Characteristics

MST236A054U						
Parameter	Symbol	Conditions	Minimum	Typical	Maximum	Units
Reverse Stand-Off Voltage	V_{RWM}	Pin5 to pin2 T=25°C			5.0	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1\text{mA}$ Pin 5 to pin2	6.0			V
Reverse Leakage Current	I_R	$V_{RWM}=5\text{V}$, $T=25^\circ\text{C}$ Pin 5 to pin2			5	μA
Forward Voltage	V_F	$I_T=10\text{mA}$		0.8	1	V
Clamping Voltage	V_C	$I_{PP}=6\text{A}$, $t_p=8/20\mu\text{s}$ I/O pin to GND		17.5	20	V
Junction Capacitance	C_j	$V_R=0\text{V}$, $f=1\text{MHz}$ I/O pin to GND		0.8		pF
		$V_R=0\text{V}$, $f=1\text{MHz}$ Between I/O pins		0.5		pF

Typical Characteristics

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure 3: Pulse Waveform




Figure 4: Clamping Voltage vs. Peak Pulse Current




Figure 5: Capacitance vs. Reverse Voltage





Figure 6: Forward Voltage vs. Forward Current



Outline Drawing – SOT-23-6L

PACKAGE OUTLINE		SOT-23-6L			
SYMBOL	INCHES		MILLIMETER		
	MIN	MAX	MIN	MAX	
A	0.041	0.049	1.050	1.250	
A1	0.000	0.004	0.000	0.100	
A2	0.041	0.045	1.050	1.150	
D	0.111	0.119	2.820	3.020	
E	0.059	0.067	1.500	1.700	
E1	0.104	0.116	2.650	2.950	
e	0.037(BSC)		0.950(BSC)		
e1	0.071	0.079	1.800	2.000	
L	0.012	0.024	0.300	0.600	
θ	0°	8°	0°	8°	

DIMENSIONS		
DIM	INCHES	MILLIMETERS
Z	0.141	3.60
G	0.055	1.40
P	0.037	0.95
X	0.024	0.60
Y	0.043	1.10
C	(0.098)	(2.50)

Notes

THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY. CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR COMPANY'S MANUFACTURING GUIDELINES ARE MET.