

PDFN3030 Plastic-Encapsulate MOSFETS

● Features

- $V_{DS} = -30V$
- $I_D = -25A$
- $R_{DS(on)}@V_{GS} = -10V < 16m\Omega$
- $R_{DS(on)}@V_{GS} = -4.5V < 31m\Omega$
- Trench Power LV MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speedze

Drain-source Voltage

-30 V

Drain Current

-25 Ampere


● Applications

- Power switching application
- Load switch
- Power management


● Mechanical Data

- Case: PDFN3030
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

● Function Diagram



PDFN3030



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
PDFN3030	R3	0.0218	5000	10000	80000	13"

● Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	-30
Gate-source Voltage	V_{GS}	V	± 20
Drain Current	I_D	A	-25
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	-100
Total Power Dissipation	P_D	W	30
Single pulse avalanche energy ⁽²⁾	EAS	mJ	27.5
Junction temperature	T_J	°C	-55 ~+150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	°C / W	4.2

● Static Parameter Characteristics (T_j=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =-250μA	V	-30	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-30V, V _{GS} =0V	μA	—	—	-1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250μA	V	-1.0	-1.6	-3.0
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(on)}	V _{GS} =-10V, I _D =-10A	mΩ	—	12	16
		V _{GS} =-4.5V, I _D =-7A		—	18	31
Forward Transconductance	g _{FS}	V _{DS} =-10V, I _D =-10A	S	15	—	—

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =-15V, V _{GS} =0V, f=1MHZ	pF	—	1367	—
Output Capacitance	C _{oss}			—	230	—
Reverse Transfer Capacitance	C _{rss}			—	205	—

● Switching Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =-10V, V _{DD} =-15V, I _D =-1A, R _{GEN} =6Ω	nS	—	10	—
Turn-on Rise Time	t _r		nS	—	14	—
Turn-off Delay Time	t _{D(off)}		nS	—	107	—
Turn-off fall Time	t _f		nS	—	69	—
Total Gate Charge	Q _g	V _{DS} =-15V, I _D =-10A V _{GS} =-10V	nC	—	28	—
Gate-Source Charge	Q _{gs}		nC	—	3	—
Gate-Drain Charge	Q _{gd}		nC	—	6.2	—

● Drian-Source Diode Characteristics

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =-10A, V _{GS} =0V	V	—	—	-1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	-25







Note :

(1)Repetitive Rating: Pulse width limited by maximum junction temperature.






(2)EAS condition : T_j=25°C ,VDD=-15V,VG=-10V,L=0.5mH,IAS=-10.5A,Rg=25Ω.

(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)





● Package Outline Dimensions (PDFN3030)





● Suggested Pad Layout





1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

