


COIL:

RESISTANCE	90 Ω ±10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.7 VDC
MUST RELEASE	1.0 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 13 MS MAX.
RELEASE TIME 5 MS MAX.
CONTACT BOUNCE 5 MS MAX. (NC)
2 MS MAX. (NO)

CUSTOMER DATA SHEET



CONTACT RATING: 10A 30 VDC RES
10A 115 VAC 400 Hz, 6A 30 VDC
INDUCTIVE 100,000 OPERATIONS

DR. R.B. 4-16-91 | CK. A/16/91 [illegible]

Communications Instruments, Inc.

CUST. HI-G
CUST. NO. 2T-1B-112

TYPE 07 RELAY

B07B932BZ1-8004