



300V 15A 24-12AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 5.0mm (.197")/5.08mm (.200")

Materials
 Housing: PA66 (UL 94V-0)
 Wire Cage: Brass, Nickel Plated
 Solder Pin: Brass, Tin Plated
 Screw: M2.5, Steel (A3), Zinc Plated
 Torque: 0.4N.m

序号/Revno. 更改记录/Revision note 签名/Signature 日期/Date

| | | | | |
|----------------|---------------|---------------|----------------|---|
| 设计/Designed by | 绘图/Drawing by | 审核/Checked by | 批准/Approved by | 未注公差 General Tolerance |
| | | | | X: ±0.2 X: ±2° .X ±0.1 .X° ±1° .XX ±0.05 .XX° ±0.5° .XXX ±0.01 |
| 图名/Title | | 文件编号/File No. | | |
| XY128V-A 5.0 | | | | |
| 页序/Sheet | | | | |
| 5.08 | | | | |
| 备注/Remark | | | | 单位/Units: mm |

 新莱亚电子
 XINLATAI ELECTRONIC CO., LTD