TO-252 Plastic-Encapsulate MOSFETS

Features


- V_{DS}=100V
- I_D=8A
- $R_{DS(on)}$@V_{GS}=10V ＜ 110mΩ
- $R_{DS(on)}$@V_{GS}=4.5V ＜ 150mΩ
- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology

Drain-source Voltage
100 V
Drain Current
8 Ampere

Applications

- Load Switch
- PWM Application
- Power Management


TO-252



Mechanical Data

- Case: TO-252
  Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
TO-252	R3	0.305	2500	5000	25000	13''

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	100
Gate-source Voltage	V_{GS}	V	±20
Drain Current	I_D	A	8
Pulsed Drain Current [1]	I_{DM}	A	32
Total Power Dissipation	P_D	W	32
Single pulse avalanche energy[2]	EAS	mJ	6.25
Junction temperature	T_J	°C	150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	°C / W	3.9

HJC Confidential

Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV_{DSS}	V_{GS}= 0V, I_D=250μA	V	100	—	—
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS}=100V, V_{GS}=0V	μA	—	—	1.0
Gate-Body Leakage Current	I_{GSS}	V_{GS}= ±20V, V_{DS}=0V	nA	—	—	±100
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS}= V_{GS}, I_D=250μA	V	1.0	1.7	2.5
Static Drain-Source On-Resistance (3)	$R_{DS(ON)}$	V_{GS}= 10V, I_D=3A	mΩ	—	95	110
		V_{GS}= 4.5V, I_D=1A		—	117	150

Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C_{iss}	V_{DS}=25V, V_{GS}=0V, f=1MHZ	pF	—	223	—
Output Capacitance	C_{oss}			—	98	—
Reverse Transfer Capacitance	C_{rss}			—	27	—

Switching Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	$t_{D(on)}$	V_{GS}=10V, V_{DD}=50V, I_D=3A ,R_{GEN}=3Ω	nS	—	12.6	—
Turn-on Rise Time	t_r		nS	—	19	—
Turn-off Delay Time	$t_{D(off)}$		nS	—	20	—
Turn-off fall Time	t_f		nS	—	27.8	—
Total Gate Charge	Q_g	V_{DS}=50V, I_D=3A V_{GS}=10V	nC	—	4	—
Gate-Source Charge	Q_{gs}		nC	—	0.9	—
Gate-Drain Charge	Q_{gd}		nC	—	1.1	—

Drian-Source Diode Characteristics

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V_{SD}	I_S=8A, V_{GS}=0V	V	—	—	1.2
Maximum Body-Diode Continuous Current	I_S	—	A	—	—	8

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=50V,VG=10V,L=0.5mH,IAS=5A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 0.5%.

HJC Confidential

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Fig.1 Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current and Gate Voltage




Fig.4 On-Resistance vs. Junction Temperature




Fig.5 Typical Body-Diode Forward Characteristics




Fig.6 Capacitance Characteristics

HJC Confidential

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Fig.7 Gate Charge




Fig.8 V(BR)DSS vs.Junction Temperature




Fig.9 Safe Operation Area





Fig.10 Normalized Maximum Transient Thermal Impedance


HJC Confidential

Package Outline Dimensions (TO-252)



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A2	0.90	1.10	0.035	0.043
b	0.66	0.86	0.026	0.034
b1	5.10	5.46	0.201	0.215
b2	4.27	4.37	0.168	0.172
b3	0.78	0.90	0.031	0.035
c	0.46	0.58	0.018	0.023
D	6.00	6.20	0.236	0.244
D1	5.35 REF.		0.211REF.	
E	6.50	6.70	0.256	0.264
E1	4.83 REF.		0.190 REF.	
e	2.18	2.38	0.086	0.094
H	9.80	10.4	0.386	0.409
L1	2.90 REF.		0.114 REF.	
L3	0.90	1.20	0.035	0.047
L4	0.60	1.00	0.024	0.039
L5	1.6 REF.		0.063 REF.	
L6	-	0.12	-	0.005


Suggested Pad Layout




Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
a	3.70	-	0.146	-
b	4.37	-	0.172	-
X	-	5.80	-	0.228
X1	-	1.20	-	0.047
Y	-	5.85	-	0.230
Y1	-	2.00	-	0.079


HJC Confidential


1.Gate Charge Test Circuit & Waveforms







2. Resistive Switching Test Circuit & Waveforms







3.Unclamped Inductive Switching (UIS) Test Circuit & Waveforms





4.Diode Recovery Test Circuit & Waveforms





HJC Confidential