



Section: A-A



Section: B-B



Section: C-C

■ Specifications(规格):

- Voltage rating(额定电压): 250V AC / DC
- Current rating(额定电流): 3A AC / DC
- Withstanding voltage(耐压值): 1000V AC/minute
- Temperature range(工作温度): -25°C~+85°C
- Insulation resistance(绝缘电阻): $\geq 1000M\Omega$
- Contact resistance(接触电阻): $\leq 10m\Omega$
- After environmental testing(环境测试后): $\leq 20m\Omega$

X8821 T M-P SN X-X

① ② ③ ④ ⑤ ⑥ ⑦

①系列

②类别:

T-端子

③外观形态:

M-公端

④材质:

P-磷铜

⑤电镀类别:G**-镀金 V**-镀全金

*01-Gold Flash *02-2U" *03-3U" *05-5U"

*10-10U" *15-15U" *30-30U" *50-50U"

SN-镀亮锡(70-120U") SN1-镀亮锡(120U"Min.)

0-素材 SW-镀雾锡

⑥电镀方式:

空码-先冲后镀 B-先镀后冲

⑦模号/MARK及特殊码

X8821TM-PSN	Phosphor Bronze	AWG#22-26	1.90mm(Max)	Stamping Before Plating:30-50u" Ni;70-120u"Sn	X8821HF
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

REVISIONS
 Authorized Signature(s)

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	X8821TM-PSN
CHKD		DATE		UNIT: mm	PART NO.: 2.50 mm Crimp Style connectors
APPD		DATE		SIZE: A4	DWG NO.:
				WEIGHT	SHEET
				1.0g	1/1
				REVISION	A0

XKB INDUSTRIAL PRECISION CO., LIMITED

ANGULAR	$\pm 5^\circ$
$L \leq 4$	± 0.2
$4 < L \leq 16$	± 0.3
$16 < L \leq 63$	± 0.4
$L > 63$	± 0.5

UNSPECIFIED TOLERANCES