PINTECH 品致®

OSCILLOSCOPE PROBE CP260N



Characteristic

■ The oscilloscope probe CP series is the most widely used oscilloscope probe. At the same time, it is the most durable and economical probe. There are no active components such as transistors or amplifiers in passive probes, so there is no need to power the probe.

Model	CP260N
Feature	Economical
Attenuation Ratio	1X,10X
Accuracy	±1%
Bandwidth	1X:DC-6MHz 10X:DC-60MHz
Rise time	1X:58ns 10X:5.8ns
Input impedance	1X:1MΩ 10X:10MΩ
Input capacitance	1X:91pF 10X:18pF
Working voltage	1X:300V 10X:600V
Working Temperature	0~50°C
Cable length	1.2m
Weight	87g

● ACCESSORIES



Insulated Tip | Measuring Tip | Spring Hook | Adjustment Tool | Channel Identifier

GUANGZHOU PINTECH CO.,LIMITED
Web:www.pintech.com.cn
Tel:86-20-82510899
E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.