

NOTES:
 Current Rating:1.5AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA9T+30%GF(UL94V-0)


Ordering Information

3111-XX R XX B K00 X 1

No. of Pins	Contact Plating	Color Insulator	Packaging
10 30	G0=Gold Flash	B=Black	A=Tray
14 34	G1=3u"Gold	U=Blue	T=Tube
16 40	G2=5u"Gold	W=White	
20 44	G3=10u"Gold		
24 50	G4=15u"Gold		
26 60	G5=30u"Gold		

S0=Gold Flash/Tin
 S1=3u"Gold/Tin
 S2=5u"Gold/Tin
 S3=10u"Gold/Tin
 S4=15u"Gold/Tin
 S5=30u"Gold/Tin
 SN=Tin

Item	Contact Length	Mating
Standard	4.00	5222 5224 5225
Alternate		



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A0	2012/05/31	NEW		X.X	TsingSn	2012/05/31	UNIT	mm	3111-XXXXXXBK00X1	2.00 BOX HEADER 90° H=5.7	Tel: +86 769 85358920	Tel: +86 512 57468408
				X.XXX	CHECK	DATE	SIZE	A4			Fax: +86 769 85358915	Fax: +86 512 57468468
				Angle	APPROVE	DATE	SHEET	1/1	Customer NO.		E-mail: sales@wcon.com	E-mail: sales@wcon.com
				± 3'			PROJ.					



Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: sales@wcon.com