

63364-1 ✓ ACTIVE

MAG-MATE

TE Internal #: 63364-1


Magnet Wire Terminals, Poke-In, Mating Tab Width .119 in [3.04 mm], Lead Wire Size 22 – 18 AWG, Lead Wire Size .3 – .8 mm²,

MAG-MATE

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Poke-In**

Mating Tab Width: **3.04 mm [.119 in]**

Mating Tab Thickness: **.46 mm [.018 in]**

Lead Wire Size: **.3 – .8 mm²**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Poke-In
Mating Tab Width	3.04 mm[.119 in]
Mating Tab Thickness	.46 mm[.018 in]
Terminal Plating Material	Tin
Terminal Orientation	Flag

Termination Features

Termination Method to Wire & Cable	Crimp, Insulation Displacement (IDC)
Crimp Area Length	3.04 mm[.12 in]

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Terminal Height	8.13 mm[.32 in]
-----------------	-----------------



Lead Wire Size	.3 – .8 mm ²
----------------	-------------------------

Magnet Wire Size	.64 – 1.02 mm
------------------	---------------

Stock Thickness (Magnet Wire Side)	.46 mm[.018 in]
------------------------------------	-----------------

Product Length	9.6 mm[.378 in]
----------------	-----------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	8000
--------------------	------

Packaging Method	Reel, Reel/Carton
------------------	-------------------

Other

Terminals & Splices Comment	Accepts stranded, fused stranded or solid lead wire.
-----------------------------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MAG-MATE



Customers Also Bought



Documents

Product Drawings

MAG-MATE TAB 22-18 018PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_63364-1_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63364-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63364-1_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English