



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.20
Pt	±0.08	±0.10	±0.10	±0.15	+0.2 -0.4
W	±0.08	±0.10	±0.10	±0.20	+0.2 -0.4
M	±0.08	±0.12	±0.12	±0.20	±0.30
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				



	Dimension
Ft±0.01	0.043
St±0.01	0.225

RoHS Compliant

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCC1606T104500-300	16	1.0	15.0	45.0	17.0	1.0	0.7	0.035	5.0	5.0	10.0	10.0	Blue
	FFCC0806T111500-300	08	1.0	7.0	115.0	9.0	1.0	0.7	0.035	5.0	5.0	10.0	10.0	Blue

4					DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation			
3		DRAWN BY: Fang		1/12-15'	TOLERANCE UNLESS OTHERWISE SPECIFIED		FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)				
2		ENGINEER: Lian		1/12-15'	.X ±	X' ± 2'	MATERIAL: SEE PRODUCT SPECIFICATION				
1		CHECKED BY: Lan		1/12-15'	.XX ±	.X' ±	CUST. CODE:				
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	1/12-15'	.XXX ±	.XX' ±	DRAWING NO. FFC001SF	FILE NO. T115013-4A	SCALE 1 / 1	SHEET 1 OF 1