

















Recommended PCB Layout(Top view)
Tolerance:±0.05mm

Specifications:
规格：
Voltage rating:125V AC/DC
额定电压：125V AC/DC
Current rating:1A AC/DC
额定电流：1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压：500V AC/分钟
Temperature range:-25℃-+105℃
温度范围：-25℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻：≥500MΩ
Contact resistance:≤20mΩ
接触电阻：≤20mΩ

X1502	W	R - 02	R -	LP	SN
①	②	③	④	⑤	⑥	⑦

1.Series No
2.Category:W-Wafer
3.Welding Board Angle:R-Stright 90°
4.Row No.Pin No:XX-02~16Pin
5.Special No:R-DIP 2.3mm
6.Material:LP-LCP UL94V-0 ,Natural
7.Plating:SN- Tin Plated

Poles	Dimensions（mm）			Poles	Dimensions（mm）		
	A	B	C		A	B	C
02	1.50	3.60	4.50	10	13.50	15.60	16.50
03	3.00	5.10	6.00	11	15.00	17.10	18.00
04	4.50	6.60	7.50	12	16.50	18.60	19.50
05	6.00	8.10	9.00	13	18.00	20.10	21.00
06	7.50	9.60	10.50	14	19.50	21.60	22.50
07	9.00	11.10	12.00	15	21.00	23.10	24.00
08	10.50	12.60	13.50	16	22.50	24.60	25.50
09	12.00	14.10	15.00				

X1502WR-02R-LPSN	LCP	Brass	X1502H
PART N0	Material	Material(Pin)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1502WR-02R-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X1502WR-02R-LPSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0