


REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE



7.62x(N-1)+9.12


13.50

NOTES1:


- UL Standard
- 1. Rated voltage/current : 300V / 15A
- 2. Torque value : M3 , 4.43Lb.in
- 3. Wire range : 22~14AWG

NOTES2:

- 1. Dimension shall be interpreted per ASME Y14.5-2009
- 2. Pitch : 7.62mm, Poles : N=02~26P
- 3. Withstanding voltage : AC1600V/1Min
- 4. Operating temperature: -40°C~+105°C
- 5. Undimensioned tolerances:




0.80±0.05



7.62x(N-1)+9.12


14.80



5.30±0.30

Pitch range in mm	Nominal dimension range		mm	mm	mm	mm	mm
	Over	TO					
6	10	30	60	100	150	0.1	1/0
TO	TO	TO	TO	TO	TO	<	<
6	10	24	30	60	100	150	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30
							±2°


6. RoHS Compliance



7.62x(N-1)+9.12

13.50

PCB LAYOUT



- (Series No.) (Poles) (Single Pitch) (Color) :1.(Grey)  
 2.(Blue)  
 3.(Black)  
 4.(Green)  
 5.(Orange)  
 6.(Red)  
 7.(Transparent)  
 8.(Yellow)  
 9.(White)

DETACHED LISTS	
PART NO.:	/
APPD:	/
CHKD:	/
DRFT:	/
THIRD ANGLE PROJECTION	
NAME:	<b>DEGSON</b> 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD
TITLE:	CUSTOMER DRAWING
DRAWING NO.:	/
REV	DO
SHEET	1/1
SCALE	1:1