




## EDG/EDS SERIES SLIDE TYPE




**EDG/EDS SPST**




**EDG/EDS DPST**




**EDG/EDS SPDT**



**EDG/EDS 3PST**



**EDG/EDS 4PST**



**EDG/EDS DPDT**

## ■ FEATURES

- Tactile response is performed directly by larger contact pressure to ensure very stable contact.
- All plastics are UL 94V-0 grade fire retardant.
- Bottom epoxy sealed standard to ensure free of flux immersion during wave soldering.
- Contact wiping on make and break.
- Gold, Silver, or Tin plated contacts to ensure low contact resistance and long mechanical life.
- Ideal for data processing, communications, remote controls and burglar alarm system use, where manual programming is required.
- RoHS Compliant

## ■ APPLICATIONS

- Numerical setting for computer terminal equipment
- Price setting for vending machines
- Programming for game machines
- Programming for industrial equipment and measuring instruments



# Switch

## ■ SPECIFICATIONS


### 1.ELECTRICAL

● Contact rating	
switching	25mA, 24VDC
non-switching	100mA
● Contact resistance	
initial	50mΩ Max.
after life test	100mΩ Max. (300mΩ Max. for Tin plated type)
● Insulation resistance	1000MΩ Min. at 100VDC
● Dielectric strength	500VDC Min. for 60 seconds
● Capacitance between adjacent switches 5pF Max.	

### 2.MECHANICAL AND ENVIRONMENTAL

● Temperature rating	
operating	-40°C to + 85°C
Storage	-40°C to + 85°C
● Operation force	800g Max. (SPST only)
● Mechanical life	2000 operations
● Humidity	95% RH, 40°C for 96 Hrs.
● Vibration	10Hz-55Hz-10Hz for 6 Hrs.
● Solderability	After flux 245±5°C for 5±1 seconds
● Resistance to soldering heat	Solder bath:260±5°C for 5±1 seconds


## ■ PART NUMBERING SYSTEM



EDS 1 08 S XX Z


- Z: RoHS Compliant (For EDS series only)
- Special product number
- Actuator and Sealing:
  - S : Standard
  - L : Low Profile Actuator
  - LT : Low Profile and Tape Sealed
  - ST : Standard and Tape Sealed
- Number of Positions: As Dimensions and Circuitry
- Contact Forms: 1. SPST 2. DPST 3. SPDT  
4. 3PST 5. 4PST 6. DPDT
- Series Name: EDS: Silver or Tin Plated Contacts

## ■ CONSTRUCTION



## DIMENSIONS AND CIRCUITRY

### EDG/EDS SPST SERIES




Dimension A

UNIT:mm(inch)

Positions	1	2	3	4	5	6	7	8	9	10	12	15
A	3.9* (0.154)	6.7 (0.264)	9.2 (0.362)	11.7 (0.461)	14.2 (0.559)	16.7 (0.657)	19.2 (0.756)	21.7 (0.854)	24.2 (0.953)	26.7 (1.051)	31.8 (1.252)	39.5 (1.555)

\* The dimensions of the 1 pole switch may vary slightly.

### EDG 33 SERIES(SPST)




Dimension A

UNIT:mm(inch)

Positions	2	3	4	5	6	7	8	9	10	12	15
A	6.7 (0.264)	9.2 (0.362)	11.7 (0.461)	14.2 (0.559)	16.7 (0.657)	19.2 (0.756)	21.7 (0.854)	24.2 (0.953)	26.7 (1.051)	31.8 (1.252)	39.5 (1.555)

Remark: 2&3 position switches don't have the "ECE" Mark.

## EDG/EDS DPST SERIES




Dimension A

UNIT:mm(inch)

Positions	1	2	3	4	5	6
A	6.7 (0.264)	11.7 (0.461)	16.7 (0.657)	21.7 (0.854)	26.7 (1.051)	31.8 (1.252)

## EDG/EDS SPDT SERIES




Dimension A

UNIT:mm(inch)

Positions	1	2	3	4	5	6
A	6.7 (0.264)	11.7 (0.461)	16.7 (0.657)	21.7 (0.854)	26.7 (1.051)	31.8 (1.252)


## EDG/EDS 3PST SERIES



Dimension A UNIT:mm(inch)

Positions	1	2	3	4	5
A	9.2 (0.362)	16.7 (0.657)	24.2 (0.953)	31.8 (1.252)	39.5 (1.555)


## EDG/EDS 4PST SERIES



Dimension A UNIT:mm(inch)

Positions	1	2	3
A	11.7 (0.461)	21.7 (0.854)	31.8 (1.252)

## EDG/EDS DPDT SERIES




Dimension A UNIT:mm(inch)



Positions	1	2	3
A	11.7 (0.461)	21.7 (0.854)	31.8 (1.252)

## OPTIONS


- ◆ RIGHT ANGLE TYPE
- DIMENSIONS AND CIRCUITRY
- DIMENSIONS A IS SAME AS PREVIOUS PAGE




## PART NUMBERING SYSTEM



### ◆ LOW PROFILE ACTUATORS



### ◆ LOW PROFILE ACTUATORS AND TOP TAPE SEALED



### ◆ SPECIAL TOP OR SIDE MARKING AVAILABLE