

2A Multi-Cell High Efficiency Switching Charger

General Description

SY6912A is a 4.0-23V input, 2A multi-cell synchronous Buck Li-Ion battery charger, suitable for portable application. Select pin is convenient for multi-cell charging. 800 kHz synchronous buck regulator integrates of 25V rating FETs with ultra low on- resistance to achieve high efficiency and simple circuit design.

Ordering Information

SY6912

 Temperature Code
 Package Code
 Optional Spec Code

Ordering Number	Package type	Note
SY6912AFCC	SO8E	

Features

- Wide Input Voltage Range: 4.0V to 23V
- High Efficiency Int. Synchronous Buck Regulator with Fixed 800kHz Switching Frequency
- Selectable for Multi-cell Charging
- Trickle Current / Constant Current / Constant Voltage Charging Mode
- Programmable (2A Max) Constant Charging Current
- Programmable Charging Timer
- Input Voltage UVLO and Battery OVP
- Over Temperature Protection
- Output Short Circuit Protection
- Automatic Shutdown Prevents Reverse Energy Flow
- Charging Status Indication
- Normal Synchronous Buck Operation when Battery Removed
- Compact package SO8E

Applications

- Cellular Telephones,
- PDA, MP3 Players, MP4 Players
- Digital Cameras
- Bluetooth Applications
- PSP Game Players, NDS Game Players
- Notebook

Typical Applications





Figure 1. SY6912A Schematic Diagram

Pinout (top view)



Top Mark: AIQxyz (device code: **AIQ**, *x=year code, y=week code, z=lot number code*)

Name	Number	Description
RS	2	Charging current program pin. Connect a current sense resistor from RS pin to BAT pin. Average charging current is detected for both TC mode and CC mode.
BAT	3	Battery positive pin.
NTC	4	Thermal protection pin. UTP threshold is about 75% V_{IN} and OTP threshold is about 30% V_{IN} . Pull up to V_{IN} can disable charging logic and make the IC operate as normal buck regulator. Pull down to ground can shutdown the IC.
CEL	5	Pull down for single-cell, pull high for 2 cells, open for 3 cells.
STAT	6	Charging status indication pin. It is open drain output pin and can be used to turn on a LED to indicate the charging in process. When the charging is done, LED is off.
LX	7	Switch node pin. This pin connects the drains of the integrated main and synchronous power MOSFET switches. Connect to external inductor.
IN	8	Positive power supply input pin. V_{IN} ranges from 4V to 23V for normal operation. It has UVLO function and must be 120mV greater than the battery voltage to enable normal operation.
TIM	1	Charging time limit pin. Connect this pin with a capacitor to ground. Internal current source charges the capacitor for TC mode and CC mode's charging time limit. TC charging time limit is about 1/9 of CC charging time.
GND	Exposed pad	Ground pin.

Absolute Maximum Ratings (Note 1)

CEL, NTC, STAT	-0.5-32V
IN, BAT, LX	-0.5-25V
TIM	-0.5- 3.6V
RS	BAT-0.3~BAT+0.3V
LX Pin current continuous	2.5A
Power Dissipation, P_D @ $T_A = 25^\circ\text{C}$, SO8E	3.3W
Package Thermal Resistance (Note 2)	
θ_{JA}	30°C/W
θ_{JC}	20°C/W
Junction Temperature Range	-40°C to 150°C
Lead Temperature (Soldering, 10 sec.)	260°C
Storage Temperature Range	-65°C to 125°C
ESD Susceptibility (Note 2)	
HBM (Human Body Mode)	2kV
MM (Machine Mode)	200V

Recommended Operating Conditions (Note 3)

CEL, NTC, STAT	-0.3-30V
IN, BAT, LX	-0.3-23V



SY6912A

TIM -----	-0.3- 3.6V
RS -----	BAT-0.1~BAT+0.1V
LX Pin current continuous -----	2A
Junction Temperature Range -----	-20°C to 125°C
Ambient Temperature Range -----	-40°C to 85°C

Electrical Characteristics

$T_A=25^{\circ}\text{C}$, $V_{IN}=15\text{V}$, $\text{GND}=0\text{V}$, $C_{IN}=10\mu\text{F}$, $L_B=2.2\mu\text{H}$, $R_S=25\text{m}\Omega$, $C_{TIM}=330\text{nF}$, unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Bias Supply (V_{IN})						
V_{IN}	Supply voltage		4.0		23	V
V_{UVLO}	V_{IN} under voltage lockout threshold	V_{IN} rising and measured from V_{IN} to GND			3.9	V
ΔV_{UVLO}	V_{IN} under voltage lockout hysteresis	Measured from V_{IN} to GND		190		mV
V_{OVP}	Input overvoltage protection	V_{IN} rising and measured from V_{IN} to GND			24	V
ΔV_{OVP}	Input overvoltage protection hysteresis	Measured from V_{IN} to GND		750		mV
Quiescent Current						
I_{BAT}	Battery discharge current	NTC pull down to GND			25	μA
I_{IN}	Input quiescent current	Disable Charging			2.0	mA
Oscillator and PWM						
f_{OSC}	Oscillator frequency		640	800	960	kHz
D	PFET duty cycle				100	%
Power MOSFET						
R_{NFET}	$R_{DS(ON)}$ of N-FET			150		$\text{m}\Omega$
R_{PFET}	$R_{DS(ON)}$ of P-FET			160		$\text{m}\Omega$
Voltage Regulation						
V_{CV}	Single-cell CV charging mode	$0^{\circ}\text{C} \leq T_A \leq 70^{\circ}\text{C}$	4.16	4.20	4.24	V
	2-cell CV charging mode		8.32	8.40	8.48	
	3-cell CV charging mode		12.48	12.60	12.72	
ΔV_{RCH}	Single-cell Voltage threshold for Recharge	$0^{\circ}\text{C} \leq T_A \leq 70^{\circ}\text{C}$	50	100	150	mV
	2-cell Voltage threshold for Recharge		100	200	300	
	3-cell Voltage threshold for Recharge		150	300	450	
V_{TRK}	Single-cell TC charging mode voltage threshold	$0^{\circ}\text{C} \leq T_A \leq 70^{\circ}\text{C}$	2.2	2.5	2.8	V
	2-cell TC charging mode voltage threshold		4.4	5.0	5.6	
	3-cell TC charging mode voltage threshold		6.6	7.5	8.4	
Battery Connect Detection						
V_{DET}	NTC voltage threshold for Battery detect	NTC Falling Edge	80%		90%	V_{IN}
t_{DET}	Detect delay time			30		ms
Charging Current						
	Internal charging current accuracy for Constant Current Mode	$I_{CC}=25\text{mV}/R_S$	-10%		10%	
	Internal charging current accuracy for Trickle Current Mode	$I_{TC}=2.5\text{mV}/R_S$	-50%		50%	
Charge Termination						
I_{TERM}	Charge Termination Current			10%		I_{CC}
T_{TERM}	Termination delay time			30		ms
Output Voltage OVP						
V_{OVP}	Output voltage OVP threshold		108%	113%	118%	V_{CV}
Output Short Protection						
V_{SHOT}	Output short protection threshold	V_{BAT} falling edge	1.70	2.00	2.30	V
f_{FBK}	Frequency fold back	$V_{BAT}<2\text{V}$		12.5%		f_{OSC}
I_{LM}	Power FET current limit			4.0		A
Timer						
T_{TC}	Trickle current charging timeout	$C_{TIM}=330\text{nF}$	0.425	0.5	0.575	hour
T_{CC}	Constant current charging timeout		3.825	4.5	5.175	hour



SY6912A


T _{MC}	Charging mode change delay time			30		ms
T _{RCHG}	Recharge time delay			30		ms
Battery Thermal Protection NTC						
UTP	Under temperature protection			70%	75%	80%
	Under temperature protection hysteresis	Falling edge			5%	
OTP	Over temperature protection			28%	30%	32%
	Over temperature protection hysteresis	Rising edge			2%	
Automatic Shutdown						
ΔV _{ASD}	ASD voltage threshold hysteresis	Measured from V _{IN} to V _{BAT}		80	240	mV
Thermal shutdown						
TSD	Thermal shutdown temperature	Rising Threshold		160		°C
TSDHYS	Thermal shutdown temperature hysteresis			20		°C

Note 1: Stresses beyond the “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Note 2: θ_{JA} is measured in the natural convection at T_A = 25°C on a low effective four-layer thermal conductivity test board of JEDEC 51-3 thermal measurement standard.

Note 3: The device is not guaranteed to function outside its operating conditions

Basic Li-Ion Battery Charge Operation Flow Chart



General Function Description

SY6912A is a 4.0-23 input, 2A multi-cell synchronous buck Li-Ion battery charger, suitable for portable application. Select pin is convenient for multi-cell charging. Integrated 800kHz synchronous buck regulator consists of 25V rating FETs with extremely low on-resistance to achieve high charging efficiency and simple circuit design.

Charging Status Indication Description

1. **Charging-In-Process** – Pull and keep STAT pin to Low;
2. **Charging Done** – Pull and keep STAT pin to High;
3. **Fault Mode** – Output high and low voltage alternatively with 0.5Hz frequency when C_{TIM} is 330nF.

Connect a LED from VIN to STAT pin, **LED ON** indicates **Charging-in-Process**, **LED OFF** indicates **Charging Done**, **LED Flash** indicates **Fault Mode**.

Buck Regulator Operation Description

If the Li-Ion battery is removed suddenly, the voltage on NTC pin increases higher than 90% V_{in} . Then, it operates as a normal peak current mode controlled synchronous buck converter and the output voltage on BAT pin is regulated at V_{CV} . In this operation mode, the constant output current loop is still active, however the charging timeout operation, termination function and the trickle current charging are disabled.

Protection Description

Thermal Protection-Thermal shutdown is active for both battery and IC. IC resumes normal work when the temperature backs in normal range again.


Short Circuit Protection- When V_{BAT} voltage is lower than the short circuit protection threshold, short circuit protection is active. In charger operation mode, the switching frequency is folded back to 12.5% of the default value and V_C is folded back to 20% of the maximum value. The trickle charging timer is still active and would timeout the IC finally. In Buck operation mode, the switching frequency is folded back to 12.5% of the default value, and the V_C initiates softstart periodically.

Over Current Protection-The internal current loop with different constant current capability is always active no matter in Buck mode or Battery Charging mode for the over current protection.


Over Voltage Protection-When V_{BAT} voltage is higher than the over voltage protection threshold no matter with or without battery connected, IC shuts down and recovers to normal work when V_{BAT} backs to normal level. Input voltage has UVLO and OVP, which would make IC shutdown and recover to normal work when the V_{IN} backs to normal range.

Timeout Protection-Programmable timeout protection is for both Trickle Current Charging Mode and Constant Current Charging Mode. Once timeout is active, IC stops the charging operation and latches off. Only power or battery re-plug in can get the latch logic reset and the IC restarted.

SO8E Package outline & PCB layout design



Recommended Pad Layout




**Notes: All dimensions are in millimeters.
All dimensions don't include mold flash & metal burr.**

Taping & Reel Specification


1. Taping orientation

SO8E



Feeding direction →

2. Carrier Tape & Reel specification for packages



Package types	Tape width (mm)	Pocket pitch(mm)	Reel size (Inch)	Trailer length(mm)	Leader length (mm)	Qty per reel
SO8E	12	8	13"	400	400	2500

3. Others: NA