



CJ9460 Series

■ INTRODUCTION:


The CJ9460 is a constant frequency, current mode step-down converter. The device integrates a main switch and a synchronous rectifier for high efficiency without an external Schottky diode. It is ideal for powering portable equipment that runs from a single cell Lithium-Ion (Li+) battery. The output voltage can be regulated as low as 0.6V. The CJ9460 can also run at 100% duty cycle for low dropout operation, extending battery life in portable system. This device offers two operation modes, PWM control and PFM Mode switching control, which allows a high efficiency over the wider range of the load.

The CJ9460 is offered in a low profile 6-pin, SOT package, and is available in an adjustable version.

■ APPLICATIONS:

- Distributed Power Systems
- Digital Set Top Boxes
- Flat Panel Television and Monitors

■ PIN CONFIGURATION:



■ FEATURES:

- High efficiency :Up to 96%
- 500kHz Constant Frequency Operation
- 2A Output Current
- No Schottky Diode Required
- 4.5V to 18V Input Voltage Range
- Output Voltage as Low as 0.6V
- Slope Compensated Current Mode Control for Excellent Line and Load Transient Response
- Integrated internal compensation
- Stable with Low ESR Ceramic Output Capacitors
- Over Current Protection with Hiccup-Mode
- Thermal Fault Protection
- Inrush Current Limit and Soft Start
- SOT-23-6L Package
- -40° C to +85° C Temperature Range

- Wireless and DSL Modems
- Notebook Computer

■ DEVICE INFORMATION:

PART NUMBER	PACKAGE
CJ9460T6	SOT-23-6L

Tabel1. Pin Description

PIN NUMBER	PIN NAME	FUNCTION
1	BS	Bootstrap. A capacitor connected between SW and BS pins is required to form a floating supply across the high-side switch driver.
2	V _{SS}	Analog ground pin.
3	FB	Adjustable version feedback input. Connect FB to the center point of the external resistor divider.
4	EN	Drive this pin to a logic-high to enable the IC Drive to a logic-low to disable the IC and enter micro-power shutdown mode.
5	V _{IN}	Power supply Pin
6	SW	Switching Pin

■ ABSOLUTE MAXIMUM RATINGS(Note1)

PARAMETER	SYMBOL	RATINGS	UNITS
Input Voltage	V _{IN}	V _{SS} -0.3~V _{SS} +20	V
EN Voltages	V _{EN}	V _{SS} -0.3~V _{SS} +20	V
FB Voltage		V _{SS} -0.3~ V _{SS} +6	V
SW Voltage		V _{SS} -0.3~V _{IN} +0.5	V
BS Voltage		V _{SW} -0.3~V _{SW} +5	V
Power Dissipation	SOT-23-6L	P _D	400
Thermal Resistance			
Operating Temperature	T _{opr}	-40~+85	°C
Junction Temperature	T _j ⁽²⁾	150	°C
Storage Temperature	T _{stg}	-40~+125	°C
Soldering Temperature & Time	T _{solder}	260°C, 10s	
ESD HBM(Human Body Mode)	-	2	kV
ESD MM(Machine Mode)	-	200	V

- 1: Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.
- 2: T_J is calculated from the ambient temperature T_A and power dissipation P_D according to the following formula: T_J = T_A + (P_D) x (170°C/W).
- 3: 100% production test at +25°C. Specifications over the temperature range are guaranteed by design and characterization.

Electrical Characteristics

($V_{IN}=V_{EN}=3.6V$, $V_{OUT}=1.8V$, $T_A = 25^{\circ}C$, unless otherwise noted.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
Input Voltage		4.5		18	V
Supply Current in Operation	$V_{EN}=2.0V$, $V_{FB}=1.1V$		0.4	0.6	mA
Supply Current in Shutdown	$V_{EN} = 0$ or $V_{EN} = GND$		1		μA
Regulated Feedback Voltage V_{FB}	$T_A = 25^{\circ}C$ $4.5V \leq V_{IN} \leq 18V$	0.588	0.600	0.612	V
High-Side Switch On-Resistance			90		m Ω
Low-Side Switch On-Resistance			70		m Ω
High-Side Switch Leakage Current	$V_{EN}=0V$, $V_{SW}=0V$		0	10	μA
Upper Switch Current Limit	Minimum Duty Cycle		2.6		A
Oscillation Frequency			0.5		MHZ
Maximum Duty Cycle	$V_{FB}=0.6V$		92		%
Minimum On-Time			60		ns
Soft-Start Time	T_{SS}		4		ms
Thermal Shutdown			160		$^{\circ}C$

TYPICAL APPLICATION CIRCUITS





Figure1 Basic Application Circuit

Note: $V_{OUT} = V_{FB} \times \left(1 + \frac{R1}{R2}\right)$

TYPICAL PERFORMANCE CHARACTERISTICS


(Test Figure1 above, unless otherwise specified)



Typical Characteristics

■ TYPICAL PERFORMANCE CHARACTERISTICS

(Test Figure1 above, unless otherwise specified)



■ FUNCTIONAL BLOCK DIAGRAM






Figure2 Block Diagram

SOT-23-6L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	2.650	2.950	0.104	0.116
E1	1.500	1.700	0.059	0.067
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

SOT-23-6L Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.