

Technical Data

Material:

Contact material: Brass  
 Plating: Gold Flash  
 Insulator material: Black polyester (H94V-0 Standard: PA6T+30%G. F


Electrical:

Current rating: 1.0amps/contact max.  
 Contact resistance:  $\leq 20m\Omega$ /contact  
 Insulation resistance:  $\geq 1000M\Omega$  at V=100V  
 Withstanding voltage: 300V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE:  $\pm 0.20$



PCB Layout

A=1.27\*nP ± 0.40

B=1.27\*nP-1.27 ± 0.20

Pin Number=1~50

APPROVALS		DATE	DRAWING NO.		SHEET 1 OF 1	
DRAWN	G.M.Chen	2015/7/17	DZ127R-11-XX-25		CONNECTION	
CHECKED			ELECTRONICS CO.,LTD		SHEET 1 OF 1	
APPROVALS			CONNECTOR		PROJ.	
TOLEFRANCES ARE		30 <sup>±0.15</sup>	±0.30	ANGLE	SCALE: 1:1	
		10 <sup>±0.10</sup>	±0.20			
		5 <sup>±0.10</sup>	±0.15			
		5	±0.10			
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.	CHECK.
	A		NEW			