
SIGN	DATE	DESCRIPTION	APPROVER
⚠			


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Wire guard: Stainless steel
- Item ③ Terminal Body(contact pin): Copper.Tin platd
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical:	cULus	IEC
Voltage rating:	600V	1000V
Current rating:	37A	76A
Wire range:	0.2-16 mm²	
Solid wire(AWG):	6-24	
Stranded wire(AWG):	6-24	
Wire strip length:	12-13mm	
Withstanding Voltage:	2.2KV	8KV
Operating temperature:	-40°C to +115°C	
Soldering temperature:	250°C±10°C/5 Sec	
Safety Approval:	c UL us	



PCB Layout

H8 xx 2 0 x 0 xxxx G

- No. OF POLES
  - 02: 2 POLES
  - :
  - :
  - 08: 8 POLES
- COLOR
  - 0: BLACK
  - 5: GREEN
  - 6: BLUE
  - 8: GREY
- G: Pb<40000ppm
- 0000: "@" Logo (Standard)
  000A: "ANYTEK" Mark
  Any special item by customer requst. please contact sales department.

POLE		2	3	4	5	6	7	8
A		30.00	50.00	70.00	90.00	110.00	130.00	150.00
B		20.00	40.00	60.00	80.00	100.00	120.00	140.00
Tol.		±0.15			±0.25			
POLE	9	10	11	12	13	14	15	16
A	170.00	190.00	210.00	230.00	250.00	270.00	290.00	310.00
B	160.00	180.00	200.00	220.00	240.00	260.00	280.00	300.00
Tol.		±0.35			±0.50			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H8 20.0mm Series					
PART NO.	H8xx20x0xxxxG			DWG NO.	8H80003	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Runner 2010.10.15	Tony 2007.06.21	UNIT: mm		X. ±0.50
				SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV.: B	X.XX ±0.10 X° ±1°