



(RECOMMENDED/P.C.B) HOLE LAYOUT

COMPONENT SIDE VIEW TOLERANCE: ±0.05

No.	ASSIGNMENT
1#	DAT2
2#	CD/DAT3 <sup>2</sup>
3#	CMD
4#	VDD
9#	CD
5#	CLK
6#	VSS
7#	DAT0
8#	DAT1



### G-Switch Specification

- Material**  
Housing: Hi-temp plastic ul 94v-0; black  
Contact: Copper alloy  
Shell: Stainless steel
- Electrical characteristics**  
Contact current rating: 0.5 amperes.  
Dielectric withstanding voltage: Ac500v r.m.s.  
Insulation resistance: 500 mw min.  
Contact resistance: 40 mw max.
- Environmental**  
Operating temperature: -40°C~+90°C
- Environmental**  
Mating cycles: 5000 insertions
- Mechanical characteristics**  
Card push insertion/out force: 0.7~1.20kgf  
Contact separation force: 0.20kgf min.

6	外壳	SUS304 T=0.15mm~ 镀镍底30u" 侧脚镀金0.5U"~平脚	1PCS
5	拉杆	SUS304~去磁	1PCS
4	滑块	LCP 黑色	1PCS
3	弹簧	SWP-B	1PCS
2	端子	C5191 T=0.15 镀Ni30U", 镀雾锡80U" 接触区域镀金1U"	1PCS
1	主体	LCP 黑色	1PCS
No.	品名	规格	数量



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:  
 X. ±0.30  
 X.x ±0.20  
 X.xx ±0.15  
 X.xxx ±0.10  
 Angles ±3°

DESIGN	陈锋枫	DATE	2022.08.24	TITLE:	
CHECKED		DATE		GT-TF003-H0185-01	
APPROVED		DATE		REV.:	X1
http://www.dg-switch.com			SCALE:	4:1	UNIT:
TEL:0769-82388879			SHEET:	1/1	