November 2012

FMS6141 Low-Cost, Single-Channel 4th-Order **Standard Definition Video Filter Driver**

Features

FAIRCHILD SEMICONDUCTOR

- Single 4th-Order 8 MHz (SD) Filter
- Drives Single, AC- or DC-coupled, Video Loads (2 V_{pp}, 150 Ω)
- Drives Dual, AC- or DC-coupled, Video Loads (2V_{pp}, 75Ω)
- **Transparent Input Clamping**
- AC- or DC-Coupled Input
- AC- or DC-Coupled Output
- **DC-Coupled Output Eliminates AC-Coupling** Capacitors
- Single Supply
- Robust 8 kV ESD Protection
- Lead-Free Packages: SOIC-8 or SC70-5

Applications

- Cable Set-Top Boxes
- Satellite Set-Top Boxes
- **DVD** Players
- **HDTVs**
- Personal Video Recorders (PVR)
- Video On Demand (VOD)

Description

The FMS6141 Low-Cost Video Filter is intended to replace passive LC filters and drivers with a low-cost integrated device. The 4th-order filter provides improved image quality compared to typical 2nd or 3rd-order passive solutions.

The FMS6141 may be directly driven by a DC-coupled DAC output or an AC-coupled signal. Internal diode clamps and bias circuitry may be used if an AC-coupled input is required (see Application Information for details).

The FMS6141's output can drive an AC- or DC-coupled single (150 Ω) or dual (75 Ω) load. DC-coupling the output removes the need for output coupling capacitors. The input DC level is offset approximately +280 mV at the output (see Application Information for details).

Related Applications Notes

- AN-6041 PCB Layout Considerations for Video Filter / Drivers
- AN-6024 FMS6xxx Product Series Understanding Analog Video Signal Clamps, Bias, DC-Restore, and AC or DC Coupling Methods



Ordering Infor	mation		
Part Number	Operating Temperature Range	Package	Packing Method
FMS6141CSX	-40°C to +85°C	8-Lead, Small Outline Integrated Circuit (SOIC)	Tape and Reel
FMS6141S5X	-40°C to +85°C	5- Lead SC70 Package	Tape and Reel
Pin Configura	tions		
VIN 1	8	Vout	



Pin Definitions

SOIC Pin #	SC70 Pin#	Name	Description	
1	3	V _{IN}	Video Input	
2		N/C	No Connect	
3	1, 2	GND	Must Be Connected to Ground	
4		N/C	No Connect	
5		N/C	No Connect	
6		N/C	No Connect	
7	5	V _{cc}	+5V Supply, Do Not Float	
8	4	V _{OUT}	Filtered Video Output	

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Min.	Max.	Unit
V _{CC}	DC Supply Voltage	-0.3	6.0	V
V _{IO}	Analog and Digital I/O	-0.3	V _{CC} +0.3	V
I _{OUT}	Output Current, Do Not Exceed		50	mA

Recommended Operating Conditions

Symbol	Parameter	Min.	Тур.	Max.	Unit
T _A	Operating Temperature Range	-40		85	°C
V _{cc}	V _{CC} Range	4.75	5.00	5.25	V

ESD Information

Symbol	Parameter	Value	Unit
ESD	Human Body Model, JESD22-A114	8.0	kV
ESD	Charged Device Model, JESD22-C101	1.5	kV

Reliability Information

Symbol	Parameter		Min.	Тур.	Max.	Unit
TJ	Junction Temperature				+150	°C
T _{STG}	Storage Temperature Range		-65		+150	°C
TL	Lead Temperature (Soldering, 10 s)				300	°C
Θ _{JA} Thermal Resistance (JEDEC Standard Multi-Layer	Thermal Resistance	SOIC-8		115		°C/W
	(JEDEC Standard Multi-Layer Test Boards, Still Air)	SC70-5		332		°C/W

DC Specifications

 $T_A = 25^{\circ}$ C, $V_{CC} = 5.0$ V, $R_S = 37.5 \Omega$; input is AC coupled with 0.1 µF; output is AC coupled with 220 µF into a 150 Ω load; unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
I _{CC}	Supply Current ⁽¹⁾	No Load		7	12	mA
V _{IN}	Video Input Voltage Range	Referenced to GND if DC- Coupled		1.4		V _{pp}
PSRR	Power Supply Rejection Ratio	DC		40		dB

Note:

1. 100% tested at 25°C

AC Electrical Specifications

 $T_A = 25^{\circ}$ C, $V_{CC} = 5.0$ V, $R_S = 37.5 \Omega$; input is AC coupled with 0.1 µF; output is AC coupled with 220 µF into a 150 Ω load; unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
AV	Channel Gain ⁽²⁾		5.6	6.0	6.4	dB
f _{1dB}	-1dB Bandwidth ⁽²⁾		4.0	6.5		MHz
f _C	-3dB Bandwidth			7.7		MHz
f _{SB}	Attenuation (Stopband Reject)	f = 27 MHz		42		dB
dG	Differential Gain			0.4		%
dφ	Differential Phase			0.4		٥
THD	Output Distortion (all channels)	V _{OUT} = 1.8 V _{pp} , 1 MHz		0.4		%
SNR	Signal-to-Noise Ratio	NTC-7 Weighting; 100 kHz to 4.2 MHz		75		dB
t _{pd}	Propagation Delay	Delay from input to output, 4.5 MHz		55		ns

Note:

2. 100% tested at 25°C

Application Information

Input Considerations

The FMS6141 Low-Cost Video Filter provides 6 dB (2X) gain from input to output. The device provides an internal diode clamp to support AC-coupled input signals. In this configuration, a 0.1 µF ceramic capacitor is used to AC couple the input signal. If the input signal does not go below ground, the clamp is inactive; but if the input signal goes below ground, the clamp circuitry sets the bottom of the sync tip (or lowest voltage) to just below ground. The input level set by the clamp, combined with the internal DC offset, keeps the output signal within an acceptable range. This clamp feature also allows the FMS6141's input to be directly driven (DC-coupled) by a ground referenced DAC output. Figure 4 shows typical DC voltage levels for the input and output signals when driven by a DC-coupled DAC output or an AC-coupled and clamped Y, CV signal.



Figure 4. Typical DC Voltage Levels

Output Considerations

The FMS6141 outputs will be DC offset from the input by 150 mv therefore $V_{OUT} = 2^*V_{IN}$ DC+150 mv. This offset is required to obtain optimal performance from the output driver and is held at the minimum value in order to decrease the standing DC current into the load. Since the FMS6141 has a 2x (6 dB) gain, the output is typically connected via a 75 Ω series back-matching resistor followed by the 75 Ω video cable. Because of the inherent divide by two of this configuration, the blanking level at the load of the video signal is always less then 1 V. When AC-coupling the output ensure that the coupling capacitor of choice will pass the lowest frequency content in the video signal and that line time distortion (video tilt) is kept as low as possible.

The selection of the coupling capacitor is a function of the subsequent circuit input impedance and the leakage current of the input being driven. In order to obtain the highest quality output video signal the series termination resistor must be placed as close to the device output pin as possible. This greatly reduces the parasitic capacitance and inductance effect on the FMS6141 output driver. Recommend distance from device pin to place series termination resistor should be no greater than 0.1 inches.



Figure 5. Distance from Device Pin to Series Termination Resistor





Layout Considerations

General layout and supply bypassing play a major role in high-frequency performance and thermal characteristics. Fairchild offers a demonstration board for the FMS6141 to guide layout and aid device evaluation. The demo board is a four-layer board with full power and ground planes. Following this layout configuration provides optimum performance and thermal characteristics for the device. For the best results, follow the steps and recommended routing rules listed below.

Recommended Routing/Layout Rules

- Do not run analog and digital signals in parallel.
- Use separate analog and digital power planes to supply power.
- Traces should run on top of the ground plane at all times.
- No trace should run over ground/power splits.
- Avoid routing at 90-degree angles.
- Minimize clock and video data trace length differences.
- Include 10 µF and 0.1 µF ceramic power supply bypass capacitors.
- Place the 0.1 µF capacitor within 0.1 inches of the device power pin.
- Place the 10 µF capacitor within 0.75 inches of the device power pin.
- For multilayer boards, use a large ground plane to help dissipate heat.
- For two-layer boards, use a ground plane that extends beyond the device body by at least 0.5 inches on all sides. Include a metal paddle under the device on the top layer.
- Minimize all trace lengths to reduce series inductance.

Thermal Considerations

Since the interior of most systems, such as set-top boxes, TVs, and DVD players are at +70°C; consideration must be given to providing an adequate heat sink for the device package for maximum heat dissipation. When designing a system board, determine

how much power each device dissipates. Ensure that devices of high power are not placed in the same location, such as directly above (top plane) and below (bottom plane) each other on the PCB.

PCB Thermal Layout Considerations

- Understand the system power requirements and environmental conditions.
- Maximize thermal performance of the PCB.
- Consider using 70 µm of copper for high-power designs.
- Make the PCB as thin as possible by reducing FR4 thickness.
- Use vias in power pad to tie adjacent layers together.
- Remember that baseline temperature is a function of board area, not copper thickness.
- Modeling techniques can provide a first-order approximation.

Power Dissipation

Consider the FMS6141's output drive configuration when calculating overall power dissipation. Care must be taken not to exceed the maximum die junction temperature. The following example can be used to calculate the FMS6141's power dissipation and internal temperature rise.

$$\begin{split} T_{J} &= T_{A} + P_{CHANNEL} \Theta_{JA} \\ \text{where } P_{CHANNEL} = V_{CC} \cdot I_{CH} + (V_{O}^{2}/R_{L}) \\ V_{O} &= 2V_{IN} + 0.280V \\ I_{CH} &= I_{CC} + (V_{O}/R_{L}) \\ V_{IN} &= RMS \text{ value of input signal} \\ I_{CC} &= 7mA \\ V_{S} &= 5V \\ R_{L} &= \text{channel load resistance} \end{split}$$

The FMS6141 is specified to operate with output currents typically less than 50 mA, which is more than sufficient for a dual (75 Ω) video load. The internal amplifiers of the FMS6141 are current limited to a maximum of 100 mA and can withstand a brief-duration short-circuit condition, but this capability is not guaranteed.



Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: <u>http://www.fairchildsemi.com/packaging/</u>.



Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: <u>http://www.fairchildsemi.com/packaging/</u>.

FMS6141 — Low-Cost, Single-Channel 4th-Order Standard Definition Video Filter Driver

FAIRCHILD SEMICONDUCTOR TRADEMARKS The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks. 2Cool™ F-PFSTM PowerTrench[®] The Power Franchise® AccuPower™ FRFET® PowerXS™ wer AX-CAP™* Global Power ResourceSM Programmable Active Droop™ GreenBridge™ QFET® BitSiC™ TinyBoost™ Green FPS™ OST Build it Now™ TinyBuck™ CorePLUS™ Green FPS™ e-Series™ Quiet Series™ TinyCalc™ RapidConfigure™ CorePOWER™ Gmax™ TinyLogic® CROSSVOLT **GTO™** \bigcirc^{M} TINYOPTO IntelliMAX™ CTL™ Saving our world, 1mW/W/kW at a time™ TinyPower™ **ISOPLANAR**TM Current Transfer Logic™ TinyPWM™ SignalWise™ Making Small Speakers Sound Louder DEUXPEED SmartMax™ TinyWire™ and Better Dual Cool™ SMART START™ TranSiC™ EcoSPARK[®] MegaBuck[™] Solutions for Your Success™ TriFault Detect™ MICROCOUPLER™ EfficientMax™ SPM TRUECURRENT®* **ESBC™** MicroFET™ **STEALTH™** uSerDes™ (R) MicroPak™ SuperFET[®] MicroPak2™ SuperSOT™-3 Fairchild® Miller Drive™ SuperSOT™-6 UHC Fairchild Semiconductor® MotionMax[™] SuperSOT™-8 Ultra FRFET™ FACT Quiet Series™ mWSaver™ SupreMOS® UniFET™ FACT OptoHiT™ FAST® SyncFET™ VCX™ OPTOLOGIC Sync-Lock™ FastvCore™ VisualMax™ **OPTOPLANAR®** SYSTEM GENERAL®* FETBench™ VoltagePlus™ FlashWriter®* XS™ i an **FPS™** * Trademarks of System General Corporation, used under license by Fairchild Semiconductor. DISCLAIMER FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS. LIFE SUPPORT POLICY FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild to combat this global problem and encourage our customers to obther part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms		
Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. 162

MS6141

I

Low-Cost, Single-Channel 4th-Order Standard Definition Video Filter Drive