

VZ 型片式铝电解电容

VZ Series Chip Type Aluminum Electrolytic Capacitors


## 特点 Features

- 低阻抗。Low impedance.
- 适用于再流焊。Reflow soldering is available.
- 适用于高密度表面组装。available for high density surface mounting.
- 工作温度范围宽 (-55°C ~ +105°C) Operating over wide temperature range.
- ROHS 指令对应完毕。Adapted to the ROHS directive.

## 主要技术性能 Specifications

项目 Items	特性 Characteristics						
工作温度范围 Operating Temperature Range	-55°C ~+105°C						
额定电压范围 Rated Voltage Range	6.3V ~ 35V						
标称电容量范围 Nominal Capacitance Range	1 ~ 220μF						
标称电容量允许偏差 Nominal Capacitance Tolerance	±20% (20°C, 120Hz)						
漏电流 Leakage Current	$I \leq 0.01C_R V_R$ or $3(\mu A)$ , 取较大者 (2分钟) $C_R$ : 标称电容量 ( $\mu F$ ) $U_R$ : 额定电压 (V) $I \leq 0.01C_R V_R$ or $3(\mu A)$ Whichever is greater(at 20°C, after 2 minutes) $C_R$ : Nominal Capacitance ( $\mu F$ ) $U_R$ : Rated voltages (V)						
损耗角正切 (tgδ) Dissipation Factor (Max) 20°C, 120Hz	$U_R$ (V)	6.3	10	16	25	35	
	$tg\delta$	0.22	0.19	0.16	0.14	0.12	
耐久性 Load Life	$+105^{\circ}\text{C}$ 施加额定电压 1000 小时后, 电容器应满足以下要求: After 1000 hours' application of rated voltage at $105^{\circ}\text{C}$ , the capacitor shall meet the following requirement:						
	电容量变化率 Capacitance Change		±20%初始值以内 Within ±20% of the initial value				
	损耗角正切 Dissipation Factor		$\leq 200\%$ 初始规定值 Not more than 200% of the initial specified value				
	漏电流 Leakage Current		$\leq$ 初始规定值 Not more than the initial specified value				
高温贮存 Shelf Life	$+105^{\circ}\text{C}$ 贮存 1000 小时后, 电容器应满足以上耐久性要求 After storage for 1000 hours at $+105^{\circ}\text{C}$ , the capacitors shall meet the requirement of load life above						
低温特性 Low Temperature Stability 阻抗比 Impedance Ratio (120Hz)	$U_R$ (V)	6.3	10	16	25	35	
	$Z(-25^{\circ}\text{C})/Z(+20^{\circ}\text{C})$	2	2	2	2	2	
	$Z(-40^{\circ}\text{C})/Z(+20^{\circ}\text{C})$	4	4	3	3	3	
耐焊接热 Resistance to Soldering Heat	在 $250^{\circ}\text{C}$ 的条件下, 电容器在热板上保持 30 秒, 然后从热板上取出电容器, 让其在室温下恢复, 电容器应满足以下要求: The capacitors shall be kept on the hot plate maintained at $250^{\circ}\text{C}$ for 30 seconds. After removing from the hot plate and restored at room temperature, they meet the following requirement.						
	电容量变化率 Capacitance Change		±10%初始值以内 Within ±10% of the initial value				
	损耗角正切 (tgδ) Dissipation Factor		$\leq$ 初始规定值 Not more than the initial specified value				
	漏电流 Leakage Current		$\leq$ 初始规定值 Not more than the initial specified value				

## 尺寸图 Dimensions



## ■ 标称电容量、额定电压、额定纹波电流与外形尺寸对应表

Nominal capacitance, rated voltage, rated ripple current and case size table

V μF	6.3			10			16			25			35			
	D×L mm	Impedance Ω	I~ mA													
1.0														4×5.4	5.0	50
1.5														4×5.4	5.0	50
2.2														4×5.4	5.0	50
3.3														4×5.4	5.0	50
4.7										4×5.4	5.0	50		4×5.4	5.0	50
6.8										4×5.4	5.0	50		5×5.4	2.6	80
10							4×5.4	5.0	50	5×5.4	2.6	80		5×5.4	2.6	80
15							5×5.4	2.6	80	6.3×5.4	1.3	115		6.3×5.4	1.3	115
22	4×5.4	5.0	50	5×5.4	2.6	80	5×5.4	2.6	80	6.3×5.4	1.3	115		6.3×5.4	1.3	115
33	5×5.4	2.6	80	5×5.4	2.6	80	6.3×5.4	1.3	115	6.3×5.4	1.3	115		6.3×7.7	0.8	150
47	5×5.4	2.6	80	6.3×5.4	1.3	115	6.3×5.4	1.3	115	6.3×7.7	0.8	150		6.3×7.7	0.8	150
68	6.3×5.4	1.3	115	6.3×5.4	1.3	115	6.3×7.7	0.8	150	6.3×7.7	0.8	150				
100	6.3×5.4	1.3	115	6.3×7.7	0.8	150	6.3×7.7	0.8	150							
150	6.3×7.7	0.8	150	6.3×7.7	0.8	150										
220	6.3×7.7	0.8	150													

└ I~ = Rated ripple current (mA) (105°C, 100KHz) I~ = 额定纹波电流 (mA) (105°C, 100KHz)

Low impedance (20°C 100KHz)

## ■ 额定纹波电流的频率系数

Frequency coefficient of ripple current

Frequency 频率	50Hz	120Hz	300Hz	1KHz	10KHz~100Hz
Coefficient 系数	0.64	0.50	0.64	0.83	1.00