

# TOA-L90303AME-B4-F

## Light Bar Display LED

Part Number	Chip		Face Color	Segment Color
	Material	Source Color		
TOA-L90303AME-B4-F	AlGaInP	Ultra orange	Black	White


### Features

- Light bar display
- Common cathoder
- I.C. compatible
- Low power requirement
- RoHS compliant

### Applications


- Audio equipment
- Instrument panels
- Symbol display

### Package Dimensions & Internal Circuit Diagram



#### Notes:

1. All dimensions are in millimeters, tolerance:  $\pm 0.25$  ; Angle:  $\pm 0.1^\circ$  unless otherwise noted.
2. Specifications are subject to change without notice.





小时  
以后用




加热中  
保温中

设置  
实际



3D 加热 标准加热



### Absolute Maximum Rating @ Ta=25°C

Parameter	Maximum Rating	Unit
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	80	mA
Power Dissipation	75	mW
Continuous Forward Current	20	mA
Recommend Operating Current	12	mA
Reverse Voltage	5	V
Operating Temperature Range	-25°C to +85°C	
Storage Temperature Range	-30°C to +85°C	
Lead-Free Solder Temperature (1/16 Inch Below Seating Plane)	260°C for 3 Sec	

### Electrical / Optical Characteristic @ Ta=25°C

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Condition	Grade
Dominant Wavelength	$\lambda_d$		623		nm	$I_F=20\text{mA}$	
Spectral Line Half-Width	$\Delta\lambda$		17		nm	$I_F=20\text{mA}$	
Forward Voltage	$V_F$	1.8	2.0	2.3	V	$I_F=20\text{mA}$	
Reverse Current	$I_R$			100	$\mu\text{A}$	$V_R=5\text{V}$	
Luminous Intensity Matching Rate	lv-m			2.0:1		$I_F=20\text{mA}$	

The DISPLAYS should be kept at 30°C or less and 60%RH or less. The DISPLAYS should be used within one year.