



**PARA LIGHT ELECTRONICS CO., LTD.**  
11F, No.8, Jiankang Rd,Zhonghe Dist,New Taipei City 253, Taiwan  
Tel: 886-2-2225-3733 Fax: 886-2-2225-4800  
E-mail: [para@para.com.tw](mailto:para@para.com.tw) <http://www.para.com.tw>

## DATA SHEET

PART NO. : L-C153PTDT-Lens-HD-U1

REV : A / 0




CUSTOMER'S APPROVAL : \_\_\_\_\_ DCC : \_\_\_\_\_

DRAWING NO. : DS-52-17-002



DATE : 2017-12-13

Page : 1

PACKAGE DIMENSIONS



Recommended Solder Pad



Note:  
Tolerance unless mentioned is  $\pm 0.1$ mm, Unit = mm.

**FEATURES**

- \* 3.2\*1.6\*1.9 mm SMD LED
- \* Fast response time
- \* Top view LED

**CHIP MATERIALS**

- \* Dice Material :Silicon
- \* Lens Color : Black

**ABSOLUTE MAXIMUM RATING : ( Ta = 25°C )**

| Parameter   | Symbol           | Rating    | Unit |
|---|------------------|-----------|------|
| Collector-Emitter Voltage                                   | V <sub>CEO</sub> | 30        | V    |
| Emitter-Collector-Voltage                                   | V <sub>ECO</sub> | 5         | V    |
| Collector Current   | I <sub>C</sub>   | 20        | mA   |
| Operating Temperature                                       | T <sub>opr</sub> | -25 ~ +85 | °C   |
| Storage Temperature   | T <sub>stg</sub> | -40 ~ +85 | °C   |
| Soldering Temperature                                       | T <sub>sol</sub> | 260       | °C   |
| Power Dissipation at(or below)<br>25°C Free Air Temperature | P <sub>c</sub>   | 75        | mW   |

**ELECTRO-OPTICAL CHARACTERISTICS : ( Ta = 25°C )**

| Parameter                            | Symbol               | Min. | Typ. | Max. | Unit | Condition   |
|--------------------------------------|----------------------|------|------|------|------|---|
| Rang Of Spectral Band width          | $\lambda_{0.5}$      | 730  | ---  | 1100 | nm   | ---   |
| Wavelength Of Peak Sensitivity       | $\lambda_p$          | ---  | 940  | ---  | nm   | ---   |
| Collector-Emitter Breakdown Voltage  | BV <sub>CEO</sub>    | 60   | ---  | ---  | V    | I <sub>c</sub> =500μA<br>Ee=0mW/cm <sup>2</sup>                     |
| Emitter-Collector Breakdown Voltage  | BV <sub>ECO</sub>    | 7    | ---  | ---  | V    | I <sub>e</sub> =50μA<br>Ee=0mW/cm <sup>2</sup>                      |
| Collector-Emitter Saturation Voltage | V <sub>CE(sat)</sub> | ---  | ---  | 0.4  | V    | I <sub>c</sub> =5mA<br>Ee=1m W/cm <sup>2</sup>                      |
| Collector Dark Current               | I <sub>CEO</sub>     | ---  | ---  | 50   | nA   | V <sub>CE</sub> =10V<br>Ee=0mW/cm <sup>2</sup>                      |
| On State Collector Current           | I <sub>C(ON)</sub>   | 0.3  | ---  | 7.0  | mA   | V <sub>CE</sub> =5V<br>Ee=1mW /cm <sup>2</sup>                      |
| Rise Time                            | t <sub>r</sub>       | ---  | 15   | ---  | μS   | V <sub>CE</sub> =5V<br>I <sub>c</sub> =1mA<br>R <sub>L</sub> =1000Ω |
| Fall Time                            | t <sub>f</sub>       | ---  | 15   | ---  |      |   |

Typical Electro-Optical Characteristics Curves

25°C Ambient Temperature Unless Otherwise Noted

Fig.1-Collector Power Dissipation vs. Ambient Temperature




Fig.2-Spectral Sensitivity




Fig.3-Relative Collector Current vs. Ambient Temperature




Fig.4-Collector Current vs. Irradiance




Fig.5-Collector Dark Collector Current vs. Ambient Temperature






Fig.6-Collector Current vs. Collector-Emitter Voltage




Reel Dimensions




Note:  
Tolerances unless mentioned  $\pm 0.1$ mm, Unit = mm.

Carrier Tape Dimensions: Loaded Quantity 2000 pcs Per Reel



Note:  
1. Tolerance unless mentioned is  $\pm 0.1$ mm, Unit = mm.  
2. Minimum packing amount is 1000 pcs per reel.

**Moisture Resistant Packing Process**



**Reliability Test Items and Conditions**

The reliability of products shall be satisfied with items listed below.  
 Confidence level : 90%  
 LTPD : 10%

| No. | Items                                  | Test Condition                                 | Test Hours/Cycles | Sample Size | Ac/Re |
|-----|--|--|-------------------|-------------|-------|
| 1   | Reflow Soldering                       | Temp. : 260°C/10sec.                           | 6 Min.            | 22 PCS.     | 0/1   |
| 2   | Thermal Shock                          | H : +100°C 5min<br>↓ 10 sec<br>L : -10°C 5min  | 300 Cycles        | 22 PCS.     | 0/1   |
| 3   | Temperature Cycle                      | H : +100°C 15min<br>↓ 5 min<br>L : -40°C 15min | 300 Cycles        | 22 PCS.     | 0/1   |
| 4   | High Temperature/Humidity Reverse Bias | Ta=85°C,85%RH                                  | 1000 Hrs.         | 22 PCS.     | 0/1   |
| 5   | Low Temperature Storage                | Ta=-40°C                                       | 1000 Hrs.         | 22 PCS.     | 0/1   |
| 6   | High Temperature Storage               | Ta=100°C                                       | 1000 Hrs.         | 22 PCS.     | 0/1   |
| 7   | DC Operation Life                      | Vce=5V   | 1000 Hrs.         | 22 PCS.     | 0/1   |

### Precautions for Use

1. Over-current-proof

Customer must apply resistors for protection; otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

2.1 Do not open moisture proof bag before the products are ready to use.

2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.


2.3 After opening the package: The LED's floor life is 1 year under 30°C or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment: 60±5°C for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile



3.2 Reflow soldering should not be done more than two times.

3.3 When soldering, do not put stress on the LEDs during heating.

3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.