

## ESD9N5B

**1-Line, Bi-directional, Normal-Capacitance, Transient Voltage Suppressor**

<http://www.sh-willsemi.com>

### Descriptions


The ESD9N5B is a Bi-directional transient voltage suppressor (TVS) to protect sensitive electronic components from electrostatic discharge (ESD). It is particularly well-suited for cellular phones, PMP, MID, PDA, digital cameras and other electronic equipment.



**DFN1006-2L (Bottom View)**

The ESD9N5B may be used to provide ESD protection up to  $\pm 30\text{kV}$  (contact and air discharge) according to IEC61000-4-2, and withstand peak pulse current up to 8A (8/20 $\mu\text{s}$ ) according to IEC61000-4-5.

The ESD9N5B is available in DFN1006-2L package. Standard products are Pb-free and Halogen-free.



**Pin configuration**

### Features

- Reverse stand-off voltage:  $\pm 5\text{V}$  Max
- Transient protection for each line according to IEC61000-4-2 (ESD):  $\pm 30\text{kV}$  (Contact and Air)  
IEC61000-4-4 (EFT): 40A (5/50ns)  
IEC61000-4-5 (surge): 8A (8/20 $\mu\text{s}$ )
- Capacitance:  $C_J = 17.5\text{pF}$  typ.
- Low leakage current:  $I_R < 1\text{nA}$  typ.
- Low clamping voltage
- Solid-state silicon technology



\* = Month (A~Z)

B = Device code  
Marking

### Order information


Device	Package	Shipping
ESD9N5B-2/TR	DFN1006-2L	10000/Tape&Reel

### Applications

- Cell phone
- PMP
- MID
- PDA
- Digital camera
- Other electronics equipment

**Absolute maximum ratings**

Parameter	Symbol	Rating	Unit
Peak pulse power ( $t_p=8/20\mu s$ )	Ppk	96	W
Peak pulse current ( $t_p=8/20\mu s$ )	I <sub>PP</sub>	8	A
ESD according to IEC61000-4-2 air discharge	V <sub>ESD</sub>	±30	kV
ESD according to IEC61000-4-2 contact discharge		±30	
Junction temperature	T <sub>J</sub>	125	°C
Operating temperature	T <sub>OP</sub>	-40~85	°C
Lead temperature	T <sub>L</sub>	260	°C
Storage temperature	T <sub>STG</sub>	-55~150	°C







**Electrical characteristics (T<sub>A</sub>=25 °C, unless otherwise noted)**

**Definitions of electrical characteristics**

**Electronics characteristics (Ta=25 °C, unless otherwise noted)**


Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	$V_{RWM}$				$\pm 5.0$	V
Reverse leakage current	$I_R$	$V_{RWM} = 5.0V$			1	$\mu A$
Reverse breakdown voltage	$V_{BR}$	$I_{BR} = 1mA$	5.6		8.5	V
Reverse holding voltage	$V_{HOLD}$	$I_{HOLD} = 50mA$	5.6		8.5	V
Clamping voltage <sup>1)</sup>	$V_{CL}$	$I_{PP} = 16A, t_p = 100ns$		11		V
Clamping voltage <sup>2)</sup>	$V_{CL}$	$V_{ESD} = 8kV$		11		V
Clamping voltage <sup>3)</sup>	$V_{CL}$	$I_{PP} = 1A, t_p = 8/20\mu s$			9	V
		$I_{PP} = 8A, t_p = 8/20\mu s$			12	V
Junction capacitance	$C_J$	$V_R = 0V, f = 1MHz$		17.5	22	pF
		$V_R = 5.0V, f = 1MHz$		11.5	15	pF

Notes:


- 1) TLP parameter:  $Z_0 = 50\Omega$ ,  $t_p = 100ns$ ,  $t_r = 2ns$ , averaging window from 60ns to 80ns.  $R_{DYN}$  is calculated from 4A to 16A.
- 2) Contact discharge mode, according to IEC61000-4-2.
- 3) Non-repetitive current pulse, according to IEC61000-4-5.

**Typical characteristics (Ta=25°C, unless otherwise noted)**

**8/20μs waveform per IEC61000-4-5**

**Contact discharge current waveform per IEC61000-4-2**

**Clamping voltage vs. Peak pulse current**

**Capacitance vs. Reverse voltage**

**Non-repetitive peak pulse power vs. Pulse time**

**Power derating vs. Ambient temperature**


**Typical characteristics ( $T_A=25^\circ\text{C}$ , unless otherwise noted)**








**ESD clamping**  
(+8kV contact discharge per IEC61000-4-2)



**ESD clamping**  
(-8kV contact discharge per IEC61000-4-2)



**TLP Measurement**

**Package outline dimensions**
**DFN1006-2L**

**Top View**

**Bottom View**

**Side View**

**Recommend land pattern (Unit: mm)**


Symbol	Dimensions In Millimeters		
	Min.	Typ.	Max.
A	0.340	-	0.530
A1	0.000	-	0.050
A3	0.125 REF.		
D	0.950	1.000	1.075
E	0.550	0.600	0.675
b	0.200	0.250	0.300
L	0.450	0.500	0.550
e	0.650 Typ.		

**Notes:**

This recommended land pattern is for reference purposes only. Please consult your manufacturing group to ensure your PCB design guidelines are met.