



# One Cell Li-ion and Li-poly Battery Protection IC

## Pin Description

## Pin Configuration




Figure2. Pin Configuration

Top Marking: MKYLL (device codeMK, Y=year code, LL= lot number code)

## Pin Description

Pin	Name	Function
1	NC	No connect
2	GND	Grounding end, battery core negative pole
3	VDD	Power Supply Pin
4	VM	Charger minus voltage input pin
5	VM	Charger minus voltage input pin

## Order Information

Marking	Part No.	Model	Description	Package	T/R Qty
MKYLL	7070230	AP6685	AP6685One Cell Liion and Lipoly Battery Protection IC3A, SOT235	SOT23-5	3000 PCS

Note (1): All All POWER parts arePbFree and adhere to the RoHS directive.

# One Cell Li-ion and Li-poly Battery Protection IC

## Specifications

### Absolute Maximum Ratings <sup>(1) (2)</sup>

Item	Min	Max	Unit
VDD Input Voltage	-0.3	6	V
VM Input Voltage	-6	10	V
Power dissipation	Internally Limited		
Operating Junction Temperature, $T_J$	-40	150	°C
Storage Temperature, $T_{stg}$	-55	150	°C
Operating Temperature Range	-40	85	°C
Lead Temperature (Soldering, 10sec.)		260	°C

Note (1): Exceeding these ratings may damage the device.

Note (2): The device is not guaranteed to function outside of its operating conditions.

### ESD Ratings

Item	Description	Value	Unit
$V_{(ESD-HBM)}$	Human Body Model (HBM) ANSI/ESDA/JEDEC JS001-2014 Classification, Class: 2	±2000	V
$V_{(ESD-CDM)}$	Charged Device Model (CDM) ANSI/ESDA/JEDEC JS002-2014 Classification, Class: C0b	±200	V
$I_{LATCH-UP}$	JEDEC STANDARD NO.78E APRIL 2016 Temperature Classification, Class: I	±150	mA

### Recommended Operating Conditions

Item	Min	Max	Unit
Operating junction temperature	-40	125	°C
Operating temperature range	-40	85	°C

Note (1): All limits specified at room temperature ( $T_A = 25^\circ\text{C}$ ) unless otherwise specified. All room temperature limits are 100% production tested. All limits at temperature extremes are ensured through correlation using standard Statistical Quality Control (SQC) methods. All limits are used to calculate Average Outgoing Quality Level (AOQL).

### Thermal Information

Item	Description	Value	Unit
$R_{JA}$	Junction-to-ambient thermal resistance <sup>(1)(2)</sup>	180	°C/W
$R_{JC(top)}$	Junction-to-case (top) thermal resistance	130	°C/W
$R_{JB}$	Junction-to-board thermal resistance	45	°C/W
$\theta_{JT}$	Junction-to-top characterization parameter	35	°C/W
$\theta_{JB}$	Junction-to-board characterization parameter	45	°C/W

Note (1): The package thermal impedance is calculated in accordance to JEDEC 51

Note (2): Thermal Resistances were simulated on JEDEC board.

# One Cell Li-ion and Li-poly Battery Protection IC

## Electrical Characteristics (1)

Parameter	Symbol	Test Conditions	Min	Typ.	Max	Unit
<b>Detection Voltage</b>						
Overcharge Detection Voltage	$V_{CU}$		4.25	4.3	4.35	V
Overcharge Release Voltage	$V_{CL}$		4.05	4.1	4.15	V
Overdischarge Detection Voltage	$V_{DL}$		2.3	2.4	2.5	V
Overdischarge Release Voltage	$V_{DR}$		2.9	3.0	3.1	V
Charger Detection Voltage	$*V_{CHA}$			-0.12		V
<b>Detection Current</b>						
Overdischarge Current Detection	$*I_{IOV1}$	$V_{DD}=3.6V$	2.7	3.5	4.4	A
Load Short-Circuiting Detection	$*I_{SHORT}$	$V_{DD}=3.6V$	10	20	30	A
<b>Current Consumption</b>						
Current Consumption in Operation	$I_{OPE}$	$V_{DD}=3.6V$ $V_M=0V$	2	2.5	5	A
Current Consumption in power Down	$I_{PDN}$	$V_{DD}=2.0V$ $V_M$ floating	1	1.5	3	A
<b>VM Internal Resistance</b>						
Resistance between VM and $V_{DD}$	$*R_{VMD}$	$V_{DD}=3.6V$ $V_M=1.0V$	100	300	500	k $\Omega$
Resistance between VM and GND	$*R_{VMS}$	$V_{DD}=2.0V$ $V_M=1.0V$	10	20	40	k $\Omega$
<b>FET on Resistance</b>						
Equivalent FET on Resistance	$*R_{SS(ON)}$	$V_{DD}=3.6V$ $I_{VM}=1.0A$	40	50	60	m $\Omega$
<b>Over Temperature Protection</b>						
Over Temperature Protection	$*T_{SHD+}$			130		•
Over Temperature Recovery Degree	$*T_{SHD-}$			100		•
<b>Detection Delay Time</b>						
Overcharge Voltage Detection Delay Time	$t_{CU}$		80	128	200	mS
Overdischarge Voltage Detection Delay Time	$t_{DL}$		30	60	120	mS
Overdischarge Current Detection Delay Time	$*t_{IOV}$	$V_{DD}=3.6V$	5	10	20	mS
Load Short-Circuiting Detection Delay Time	$*t_{SHORT}$	$V_{DD}=3.6V$	100	200	400	S

Note (1): \*The parameter is guaranteed by design.

# One Cell Li-ion and Li-poly Battery Protection IC


## Typical Performance Characteristics (1) (2)

Note(1): Performance waveforms are tested on the evaluation board.

Note(2):  $V_{IN}=4.5V, R_1=1K, C_1=0.1\mu F, T_A = +25^\circ C$ , unless otherwise noted.


Supply Current Vs.  $V_{IN}$

$V_{DD}=0-6V$




GND to VM On Resistance Vs.  $I_{OUT}$

$V_{DD}=3.6V$




Power On

$R_{BAT}=5\ \Omega$




Power Off


$R_{BAT}=5\ \Omega$



Battery Charging On




Battery Charging Off




Battery Charging, OCP

$I_{BAT} = 2.2A$




Battery Charging OVP

$V_{BAT} = 3.9V$




Overdischarge Protection UVP

Reduce  $V_{OUT}$  to UVP Point




Overdischarge Protection OCP

Increase  $I_{OUT}$  to OCP Point




SCP Entry

Short Charger+ to Charger-



OTP

$I_{BAT}=2A$ , Increase  $T_{SHD+}$  to 130°C



# One Cell Li-ion and Li-poly Battery Protection IC

## Functional Block Diagram




Figure3. FunctionalBlock Diagram

## Functions Description

The AP6685 monitors the voltage and current of a battery and protects it from being damaged due to overcharge voltage, over discharge voltage, over discharge current, and short circuit conditions by disconnecting the battery from the load or charger. These functions are required in order to operate the battery cell within specified limits. The device requires only one external capacitor. The MOSFET is integrated and its  $R_{DS(on)}$  is as low as 50mΩ typical.

## Normal Operating Mode

If no exception condition is detected, charging and discharging can be carried out freely. This condition is called the normal operating mode.

## Overcharge Status

When the battery voltage becomes higher than the overcharge detection voltage ( $V_{OC}$ ) during charging under normal condition and the state continues for the overcharge detection delay time ( $t_{OD}$ ), the AP6685 turns the charging control FET off to stop charging. This condition is called the overcharge status. The overcharge condition is released in the following two cases:

1. When the battery voltage drops below the overcharge release voltage ( $V_{OR}$ ), the AP6685 turns the charging control

## One Cell Li-ion and Li-poly Battery Protection IC

FET on and returns to the normal condition.

2. When a load is connected and discharging starts, the AP6685 turns the charging control FET on and returns to the normal condition. The release mechanism is as follows: the discharging current flows through an internal parasitic diode of the charging FET immediately after a load is connected and discharging starts, and the VM pin voltage increases about 0.7V (forward voltage of the diode) from the GND pin voltage momentarily. The AP6685 detects this voltage and releases the overcharge condition. Consequently, in the case that the battery voltage is equal to or lower than the overcharge detection voltage ( $V_{OC}$ ), the AP6685 returns to the normal condition immediately, but in the case the battery voltage is higher than the overcharge detection voltage ( $V_{OC}$ ), the chip does not return to the normal condition until the battery voltage drops below the overcharge detection voltage ( $V_{OC}$ ). Even if the load is connected. In addition, if the VM pin voltage is equal to or lower than the overcurrent 1 detection voltage when a load is connected and discharging starts, the chip does not return to the normal condition.

**Remark** If the battery is charged to a voltage higher than the overcharge detection voltage ( $V_{OC}$ ), and even if a large load causing an overcurrent is connected, the battery voltage will not fall below the overcharge detection voltage ( $V_{OC}$ ), and the overcurrent or load short detection will be detected in the battery. It does not work until the voltage is lower than the overcharge detection voltage ( $V_{OC}$ ). However, since the internal impedance of the actual battery has several tens of  $m\Omega$ , and the battery voltage immediately drops after the connection of the heavy load causing the overcurrent, the overcurrent operates. The load short-circuit detection works properly regardless of the battery voltage.

### Over-discharge Status

When the battery voltage drops below the over-discharge detection voltage ( $V_L$ ) during discharging under normal condition and it continues for the over-discharge detection delay time ( $t_{td}$ ) or longer, the AP6685 turns the discharging control FET off and stops discharging. This condition is called over-discharge status. After the discharging control FET is turned off, the VM pin is pulled up by the  $R_{MD}$  resistor between VM and VDD in AP6685. Meanwhile when VM is bigger than 1.5V (typ.) (the load short-circuiting detection voltage), the current of the chip is reduced to the power-down current ( $I_{PDN}$ ). This condition is called power-down condition. The VM and VDD pins are shorted by the  $R_{VB}$  resistor in the IC under the over-discharge and power-down conditions. The power-down condition is released when a charger is connected and the potential difference between VM and VDD becomes 1.3V (typ.) or higher (load short-circuiting detection voltage). At this time, the FET is still off. When the battery voltage becomes the over-discharge detection voltage ( $V_L$ ) or higher (see note), the AP6685 turns the FET on and changes to the normal condition from the over-discharge condition.

**Remark** If the VM pin voltage is not less than the charger detection voltage ( $V_{CHA}$ ) and the battery voltage reaches the over-discharge release voltage ( $V_{DR}$ ) or higher, the over-discharge condition is released when the battery under over-discharge condition is connected to the charger (The discharge control FET is turned on).

### Overcurrent Status

When the discharging current becomes equal to or higher than a specified value (the VM pin voltage is equal to higher than the overcurrent detection voltage) during discharging under normal condition and the state continues for the overcurrent detection delay time or longer, the AP6685 turns off the discharging control FET to stop discharging. This condition is called overcurrent status (The overcurrent includes overcurrent, load short-circuiting.) The VM and GND pins are shorted internally by the  $R_{OB}$  resistor under the overcurrent condition. When a load is connected, the VM pin voltage equals the VDD voltage due to the load. The overcurrent condition returns to the normal condition when the load is released and the impedance between the VM pin and GND becomes

# One Cell Li-ion and Li-poly Battery Protection IC

higher than the automatic recoverable impedance. When the load is removed, the VM pin goes back to the GND potential since the VM pin is shorted to the GND pin with the P-resistor. Detecting that the VM pin potential is lower than the overcurrent detection voltage ( $V_{OV}$ ), the IC returns to the normal condition.

## Abnormal Charge Current Detection

the VM pin voltage drops below the charger detection voltage ( $V_{CHA}$ ) during charging under the normal condition and it continues for the overcharge detection delay time ( $t_{OU}$ ) or longer, the AP6685 turns the charging control FET off and stops charging. This action is called abnormal charge current detection. Abnormal charge current detection works when the discharging control FET is on and the VM pin voltage is below the charger detection voltage ( $V_{CHA}$ ). When an abnormal charge current flows into a battery in the overdischarge condition, the AP6685 consequently turns the charging control FET off and stops charging after the battery voltage becomes the overdischarge detection voltage and the overcharge detection delay time elapses.

Abnormal charge current detection is released when the voltage difference between VM pin and GND pin becomes lower than the charger detection voltage ( $V_{CHA}$ ) by separating the charger. Since the 0V battery charging function has higher priority than the abnormal charge current detection function, abnormal charge current may not be detected by the product with the 0V battery charging function while the battery voltage is low.

## Load Short-circuiting Status

If voltage of VM pin is equal or below short-circuiting protection voltage ( $V_{SHORT}$ ), the AP6685 will stop discharging and battery is disconnected from load. The maximum delay time to switch current off is  $t_{DRT}$ . This status is released when voltage of VM pin is higher than short protection voltage ( $V_{SHORT}$ ), such as when disconnecting the load.

## Delay Circuits

The detection delay time for over-discharge current and load short-circuiting starts when over-discharge current is detected. As soon as over-discharge current or load short-circuiting is detected over detection delay time for over-discharge current or load short-circuiting, the AP6685 stops discharging. When battery voltage falls below over-discharge detection voltage due to over-discharge current, the AP6685 stops discharging by over-discharge current detection. In this case the recovery of battery voltage is so slow that if battery voltage over discharge voltage detection delay time is still lower than over-discharge detection voltage, the AP6685 shifts to power-down.




Figure 4. Overcurrent delay time



# One Cell Li-ion and Li-poly Battery Protection IC

## 0V Battery Charging Function (1) (2) (3)

This function enables the charging of a connected battery whose voltage is 0V by charge. When a charger having 0V battery start charging charger voltage  $V_{CH}$  or higher is connected between B+ and B-, the charging control FET gate is fixed to VDD potential. When the voltage between the gate and the source of the charging control FET becomes equal to or higher than the overvoltage by the charger voltage, the charging control FET is turned on to start charging. At this time, the discharging control FET is off and the charging current flows through the internal parasitic diode in the discharging control FET. If the battery voltage becomes equal to or higher than the overdischarge release voltage  $V_{OL}$ , the normal condition returns.

Note (1): Some battery providers do not recommend charging of completely discharged cells. Please refer to battery providers before the selection of 0V battery charging function.

Note(2): The 0V battery charging function has higher priority than the abnormal charge current detection function. Consequently, a product with the 0V battery charging function charges a battery and abnormal charge current cannot be detected during the battery voltage is low (at most 1.8V or lower).

Note(3): When a battery is connected to the IC for the first time, the IC may not enter the normal condition in which discharging is possible. In this case, set the VM pin voltage equal to the GND voltage (or connect the VM and GND pins or connect a charger) to enter the normal condition.

## Timing Chart

### Overcharge and overdischarge detection




Figure51 Overcharge and Overdischarge Voltage Detection

**Remark:**

- (1) Normal condition
- (2) Overcharge voltage condition
- (3) Overdischarge voltage condition
- (4) Overcurrent condition

# One Cell Li-ion and Li-poly Battery Protection IC

## Overdischarge current detection




Figure52 Overdischarge Current Detection

**Remark:**

- (1) Normal condition
- (2) Overcharge voltage condition
- (3) Overdischarge voltage condition
- (4) Overcurrent condition

## Charger Detection




Figure53 Charger Detection

**Remark:**

- (1) Normal condition
- (2) Overcharge voltage condition
- (3) Overdischarge voltage condition
- (4) Overcurrent condition

# One Cell Li-ion and Li-poly Battery Protection IC

## Abnormal Charger Detection




Figure54 Abnormal Charger Detection

**Remark:**

- (1) Normal condition (2) Overcharge voltage condition
- (3) Overdischarge voltage condition (4) Overcurrent condition

## Typical Application

As shown in Figure 4, the bold line is the high density current path which must be kept as short as possible. For thermal management, ensure that these trace widths are adequate. C1 & R1 is a decoupling capacitor & resistor which should be placed close as possible to AP6685.


## Precautions

- Pay attention to the operating conditions for input/output voltage and load current so that the power loss in AP6685 does not exceed the power dissipation of the package.
- Do not apply an electrostatic discharge to this AP6685 that exceeds the performance ratings of the built-in electrostatic protection circuit.

# One Cell Li-ion and Li-poly Battery Protection IC

## Package Description

### SOT23-5



**NOTE:**

1. CONTROL DIMENSION IS IN INCHES. DIMENSION IN BRACKET IS IN MILLIMETERS.
2. PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
3. PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSIONS.
4. LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.004" INCHES MAX.
5. DRAWING CONFORMS TO JEDEC MS-012, VARIATION BA.
6. DRAWING IS NOT TO SCALE.