

**Specifications:**


规格:  
 Voltage rating:150V AC/DC  
 额定电压: 150V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:500V AC/minute  
 耐受电压: 500V AC/分钟  
 Temperature range:-25℃~+85℃  
 温度范围: -25℃~+85℃  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ  
 接触电阻: ≤20mΩ  
 After environmental testing:≤40mΩ  
 环境测试后: ≤40mΩ  
 Wire Range:#24-28  
 电线范围: #24-28  
 Insulation OD:1.10mm(Max)  
 绝缘外径: 1.10mm (最大值)


**X1503 T- P XX**

① ② ③ ④


1. Series Number
2. Category: T-terminal
3. Material: P-Phosphor bronze
4. Plating Code: V01-Gold Flash  
SN-Bright tin plating



SECTION: A-A  
SCALE: 1:1



SECTION: B-B  
SCALE: 1:1



X1503T-PV01	Phosphor Bronze	AWG#24-28	1.10mm(Max)	Stamping Before Plating:30u"Ni MIN,Gold Flash	X1503H
X1503T-PSN				Stamping Before Plating:30u"Ni MIN,70u"Sn Min	
PART NO	Material	Wire Range	Insulation OD	Finish	Suitable: XKB

广东星坤科技股份有限公司

生	日期
效	日期
效	日期
效	日期
MARK	文件工程章

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm
UNSPECIFIED TOLERANCES	

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	1.50mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.: X1503T-PXXX
KKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET
				1.0g	1/1
				REVISION	A0