

N-Channel Enhancement Mode MOSFET

TDM3436

DESCRIPTION



The TDM3436 uses advanced trench technology to provide excellent RDS(ON) and low gate charge. This device is suitable for use as a load switch or in PWM applications.

GENERAL FEATURES

- RDS(ON) < 4.1mΩ @ VGS=4.5V
RDS(ON) < 3.1mΩ @ VGS=10V
- High Power and current handling capability
- Lead free product is available
- Surface Mount Package

Application

- PWM applications
- Load switch
- Power management



ABSOLUTE MAXIMUM RATINGS(TA=25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V _{DS}	40	V
Gate-Source Voltage	V _{GS}	±20	V
Drain Current @ Continuous	I _D (T _A =25°C)	25	A
	I _D (T _A =70°C)	20	A
Drain Current @ Current-Pulsed (Note 1)	I _{DM} (T _c =25°C)	300	A
Drain Current @ Continuous	I _D (T _c =25°C)	100	A
	I _D (T _c =100°C)	78	A
Maximum Power Dissipation (T _A =25°C)	P _D	2.7	W
Maximum Operating Junction Temperature	T _J	150	°C
Storage Temperature Range	T _{STG}	-55 To 150	°C

THERMAL CHARACTERISTICS

Thermal Resistance,Junction-to-Ambient (Note 1)	R _{θJA}	50	°C/W
---	------------------	----	------

N-Channel Enhancement Mode MOSFET
TDM3436
ELECTRICAL CHARACTERISTICS ($T_A=25^{\circ}\text{C}$ unless otherwise noted)


Parameter	Symbol	Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	40	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=32V, V_{GS}=0V$	-	-	1	μA
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	± 100	nA
ON CHARACTERISTICS (Note 2)						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1.4	1.7	2.5	V
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS}=4.5V, I_D=20A$	-	3.1	4.1	m Ω
		$V_{GS}=10V, I_D=25A$	-	2.4	3.1	m Ω
DYNAMIC CHARACTERISTICS (Note 4)						
Input Capacitance	C_{iss}	$V_{DS}=20V, V_{GS}=0V, F=1.0MHz$	-	2650	-	PF
Output Capacitance	C_{oss}		-	750	-	PF
Reverse Transfer Capacitance	C_{rss}		-	88	-	PF
SWITCHING CHARACTERISTICS (Note 3)						
Turn-on Delay Time	$t_{d(on)}$	$V_{DS}=20V, R_L=20\Omega, V_{GEN}=10V, R_G=6\Omega, I_D=1A$	-	17	-	nS
Turn-on Rise Time	t_r		-	11.5	-	nS
Turn-Off Delay Time	$t_{d(off)}$		-	36	-	nS
Turn-Off Fall Time	t_f		-	31	-	nS
Total Gate Charge	Q_g	$V_{DS}=20V, I_D=25A, V_{GS}=4.5V$	-	17	-	nC
Gate-Source Charge	Q_{gs}		-	7	-	nC
Gate-Drain Charge	Q_{gd}		-	5.3	-	nC
Body Diode Reverse Recovery Time	T_{rr}	$I_F=5A, di/dt=100A/\mu s$	-	38	-	nS
Body Diode Reverse Recovery Charge	Q_{rr}		-	35	-	nC
DRAIN-SOURCE DIODE CHARACTERISTICS						
Diode Forward Voltage (Note 2)	V_{SD}	$V_{GS}=0V, I_S=20A$	-	0.8	1.1	V

NOTES:


1. Pulse width limited by max. junction temperature.
2. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.
3. Guaranteed by design, not subject to production testing

Typical Operating Characteristics


Power Dissipation




Drain Current



Safe Operation Area




Thermal Transient Impedance




Typical Operating Characteristics(Cont.)


Safe Operation Area




Thermal Transient Impedance



Output Characteristics




Drain-Source On Resistance




Typical Operating Characteristics (Cont.)


Gate-Source On Resistance




Gate Threshold Voltage



Drain-Source On Resistance




Source-Drain Diode Forward




Typical Operating Characteristics (Cont.)


Capacitance



Gate Charge




Transfer Characteristics




Package Information

DFN5*6-8 Package



DIMENSIONS	DFN5x6-8			
	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	0.90	1.20	0.035	0.047
B	0.3	0.51	0.012	0.020
C	0.19	0.25	0.007	0.010
D	4.80	5.30	0.189	0.209
D1	4.00	4.40	0.157	0.173
E	5.90	6.20	0.232	0.244
E1	5.50	5.80	0.217	0.228
e	1.27 BSC		0.050 BSC	
F	0.05	0.30	0.002	0.012
F1	0.35	0.75	0.014	0.030
G	0.05	0.30	0.002	0.012
G1	0.35	0.75	0.014	0.030
H	3.34	3.9	0.131	0.154
K	0.762	-	0.03	-

RECOMMENDED LAND PATTERN



Note : 1.Dimension D, D1,D2 and E1 do not include mold flash or protrusions.
Mold flash or protrusions shall not exceed 10 mil.

Design Notes