







Rev.	ECN Number	Description	Date	Drawn	Checkd	Approved
A	ECN150099	NEW DRAWING	10/27'14	Jason Li		




3D VIEW


- NOTES:
- MATERIAL:
1-1: STAINLESS STEEL, T=0.06mm.
 - FINISH:
2-1: 5u" MIN. Au PLATING ON CONTACT AREA,
1u" MIN. Au PLATING ON SOLDER AREA,
50~150u" NICKEL UNDERPLATING OVER ALL.
 - SPECIFICATIONS:
3-1. RATED CURRENT: 1.0A
3-2. RATED VOLTAGE: 12V
3-3. CONTACT RESISTANCE: 30mΩ MAX.
3-4. OPERATING TEMPERATURE: -20°C~+65°C.
3-5. MAX. BEAM DEFLECTION: 0.5mm. ON CONTACT POINT.
 - RF PERFORMANCE:
4-1. IMPEDANCE: 50ΩHM.
4-2. VSWR: 1.5 MAX. (DC~3GHz)
4-3. INSERTION LOSS: 0.6dB MAX. (DC~3GHz)



STATE AT WORKING HEIGHT 0.4mm



RECOMMENDED PCB LAYOUT TOLERANCE ±0.05MM



GENERAL TOLERANCE	
XX. ±0.50	X.° ±2.0°
X. ±0.35	.X° ±1.0°
.X ±0.25	.XX° ±0.5°
.XX ±0.15	

SCALE:	1:1
UNIT:	mm
SIZE:	A4

DRAWN	JASON LI
CHECK	
APPROVE	

DATE	10/27'14
DATE	
DATE	

DWG. NO.	600-3141-01
PARTS NO.(INTENDED USE)	818003141

TITLE (CUSTOMER DRAWING)
Antenna RF Spring, SMT,
Au Plating, L2.5*W1.0*H0.8mm

REV.	A
SHEET	1/1